

Specification Sheet

Part Number: PR1M4

Panel rivets are made with nylon material to hold duct securely to the panel without corroding, ensuring longevity.

Panel rivets can be easily inserted with use of a specially designed, long shafted panel rivet tool.

Ergonomic design of the tool ensures effortless use when inserting rivets into deep channels or locations difficult to access.



Panel Rivet, PA66, Natural, 1000/bg

Article Number 181-00139

Type PR1

Color Natural (NA)

Quantity Per pack

Product Description HellermannTyton panel rivets are one piece drive rivets that provide a fast, economic means of affixing wiring duct. The rivet is inserted into a 3/16" pre-punched hole and the pin is driven into the base, thereby expanding the rivet legs and locking the duct and sub-panel in place. The panel thickness (including the duct thickness) should be a maximum of 3/16".

Short Description Panel Rivet, PA66, Natural, 1000/bg

Global Part Name	PR1-PA66-NA
------------------	-------------

Minimum Tensile Strength (Imperial)	107
-------------------------------------	-----

Minimum Tensile Strength (Metric)	478
-----------------------------------	-----

Panel Thickness Min (Imperial)	0.15
--------------------------------	------

Panel Thickness Max (Imperial)	0.28
--------------------------------	------

Panel Thickness Min (Metric)	3.9
------------------------------	-----

Panel Thickness Max (Metric)	7.0
------------------------------	-----

Mounting Hole Diameter D (Imperial)	0.2
-------------------------------------	-----

Mounting Hole Diameter D (Metric)	5.0 mm
-----------------------------------	--------

Mounting Hole Diameter D Max (Metric)	5.0
---------------------------------------	-----

Material	Polyamide 6.6 (PA66)
----------	----------------------

Material Shortcut	PA66
-------------------	------

Flammability	UL 94 HB
--------------	----------

Halogen Free	Yes
--------------	-----

UV Resistant (Yes/No)	No
-----------------------	----

Use Conditions	For Indoor Use Only
Operating Temperature	-40°F to +176°F (-40°C to +80°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
 Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)