


TP 3105S - Touch panel

2400455

<https://www.phoenixcontact.com/us/products/2400455>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Touch panel with 26.4 cm/10.4" TFT-display (analog resistive (polyester)), 800 x 600 pixel(s) (SVGA), 262144 colors, Arm[®] Cortex[®]-A8, 800 MHz, 2x USB host 2.0, 1 x Ethernet (10/100 Mbps), RJ45, Windows[®] Embedded Compact 7 and user software: Visu+ / AX OPC Server. (bus system: without)

Your advantages

- Acoustic warning from alarms via integrated buzzer (85 dB)
- Energy efficient due to LED backlighting
- Visu+ RT and AX OPC server integrated as standard in all devices
- Easy IP address allocation and active connection monitoring thanks to PROFINET-Device according to Conformance Class B
- Display available in sizes from 14.5 cm (5.7") to 39.05 cm (15.4")
- Versatile communication options, even with third-party systems, thanks to numerous drivers and interfaces
- Easy installation, low installation depth, and compact design
- Short startup time

Commercial data

Item number	2400455
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DR17
Product key	DRCABC
Catalog page	Page 472 (C-6-2019)
GTIN	4055626055954
Weight per piece (including packing)	2,349 g
Weight per piece (excluding packing)	1,800 g
Customs tariff number	84714100
Country of origin	DE

TP 3105S - Touch panel

2400455

<https://www.phoenixcontact.com/us/products/2400455>



Technical data

Product properties

Product type	Operator panel
--------------	----------------

Computer data

Processor	Arm® Cortex®-A8, 800 MHz
Operating system	Windows® Embedded Compact 7
RAM	512 MB RAM
Data storage system	Flash, 1 GB
Slots	1x SD

Display

Display type	26.4 cm/10.4" TFT
Screen resolution	800 x 600 Pixel(s) (SVGA)
Touch technology	analog resistive (polyester)
Display lighting type	LED
Brightness	340 cd/m² typical (adjustable)
MTBF	50000 h
Color spectrum	262144 colors
Reading angle left	55 °
Reading angle right	55 °
Reading angle top	70 °
Reading angle bottom	70 °

Software

User software	Visu+ AX OPC Server
---------------	------------------------

System requirements

Runtime system	Visu+ Runtime
----------------	---------------

Interfaces

Interfaces	2x USB Host 2.0
Network	1 x Ethernet (10/100 Mbps), RJ45
Bus system	without

System properties

User software	Visu+ AX OPC Server
---------------	------------------------

System requirements

Runtime system	Visu+ Runtime
----------------	---------------

Electrical properties

Service life of battery	5 years (typical)
-------------------------	-------------------

TP 3105S - Touch panel



2400455

<https://www.phoenixcontact.com/us/products/2400455>

Supply

Supply voltage	24 V DC
Supply voltage range	18 V DC ... 30 V DC
Power supply unit	24 V DC $\pm$ 20 %
Typical current consumption	0.5 A

Real-time clock

Realtime clock	Yes (battery-backed)
----------------	----------------------

Supply

Power consumption	typ. 12 W
-------------------	-----------

Mounting

Mounting type	Front mounting
---------------	----------------

Material specifications

Material front plate	Aluminum (natural anodized)
Housing material	Steel sheet, zinc-plated

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65 (front), IP20 (back) NEMA 4X
Ambient temperature (operation)	0 °C ... 50 °C
Ambient temperature (storage/transport)	-25 °C ... 70 °C
Permissible humidity (operation)	20 % ... 85 % (non-condensing)
Permissible humidity (storage/transport)	20 % ... 85 % (non-condensing)
Shock	DIN EN 60068-2-27
Vibration (operation)	DIN EN 60068-2-6

Dimensions

External dimensions

Width / Height / Depth	295 mm / 220 mm / 5 mm (Dimensions of the front plate)
------------------------	--

Installation dimensions

Width / Height / Installation depth	287 mm / 212 mm / 54 mm (Installation cutout)
-------------------------------------	---

TP 3105S - Touch panel



2400455

<https://www.phoenixcontact.com/us/products/2400455>

Classifications

ECLASS

ECLASS-11.0	27330201
-------------	----------

ETIM

ETIM 8.0	EC001412
----------	----------

UNSPSC

UNSPSC 21.0	43211900
-------------	----------

TP 3105S - Touch panel

2400455

<https://www.phoenixcontact.com/us/products/2400455>



Environmental product compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 15;
	For information on hazardous substances, refer to the manufacturer's declaration available under "Downloads"

TP 3105S - Touch panel

2400455

<https://www.phoenixcontact.com/us/products/2400455>



Accessories

TOUCH PEN - Touch pen

2701379

<https://www.phoenixcontact.com/us/products/2701379>



Touch pen for analog-resistive HMI's, silver coated. Delivery includes self-adhesive pen holder.

USB FLASH DRIVE - USB memory stick

2402809

<https://www.phoenixcontact.com/us/products/2402809>



USB memory stick, 8 GB

TP 3105S - Touch panel

2400455

<https://www.phoenixcontact.com/us/products/2400455>



SD FLASH 2GB - Program / configuration memory

2988162

<https://www.phoenixcontact.com/us/products/2988162>



Program and configuration memory, for extending the internal flash memory, pluggable, 2 GB.

HMI BATTERY - Battery/accumulator

2701383

<https://www.phoenixcontact.com/us/products/2701383>

Lithium battery



TP 3105S - Touch panel

2400455

<https://www.phoenixcontact.com/us/products/2400455>



HMI SCB MOUNTING KIT 4 - Mounting material

2701384

<https://www.phoenixcontact.com/us/products/2701384>



HMI mounting kit for installation on a front plate. The mounting kit includes 4 x mounting brackets, 4 x screw threads, and a hexagonal wrench.

HMI SCB MOUNTING KIT 6 - Mounting material

2701385

<https://www.phoenixcontact.com/us/products/2701385>



HMI mounting kit for installation on a front plate. The mounting kit includes 6 x mounting brackets, 6 x screw threads, and a hexagonal wrench.

TP 3105S - Touch panel

2400455

<https://www.phoenixcontact.com/us/products/2400455>



HMI SCB MOUNTING KIT 8 - Mounting material

2701387

<https://www.phoenixcontact.com/us/products/2701387>




HMI mounting kit for installation on a front plate. The mounting kit includes 8 x mounting brackets, 8 x screw threads, and a hexagonal wrench.

MC 1,5/ 3-STF-3,5 BD:1-3 - PCB connector

1751312

<https://www.phoenixcontact.com/us/products/1751312>



PCB connector, nominal cross section: 1.5 mm², color: green, nominal current: 8 A, rated voltage (III/2): 160 V, contact surface: Tin, contact connection type: Socket, number of potentials: 3, number of rows: 1, number of positions: 3, number of connections: 3, product range: MC 1,5/...-STF, pitch: 3.5 mm, connection method: Screw connection with tension sleeve, screw head form: L Slotted, conductor/PCB connection direction: 0 °, plug-in system: COMBICON MC 1,5, locking: Screw locking mechanism, mounting: Screw flange, type of packaging: packed in cardboard

Phoenix Contact 2023 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com