



Part Number : [313874017](#)

Product Description : 2.54mm Pitch, MX123 Header, 80 Circuits Shrouded Assembly, Qty(80) 0.64mm Square Signal Pins, Harness Side Key Code G, Blue (Ag Mate Side Finish)

Series Number : 31387

Status : Active

Product Category : PCB Headers and Receptacles



Documents and Resources

Drawings

[313874017_sd.pdf](#)

[PK-31301-916-001.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[Symbol and Footprint \(Multi-Format\)](#)

Specifications

[AS-31386-200-001.pdf](#)

[PS-31387-200-001.pdf](#)

[PS-34566-0000-001.pdf](#)

[TS-31387-1658-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 33; 44
China RoHS	Not Relevant
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Not Contained per D(2023)8585-DC (23 Jan 2024)

EU RoHS

Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of ComplianceAdditional Product Compliance Information**Part Details****General**

Status	Active
Category	PCB Headers and Receptacles
Series	31387
Description	2.54mm Pitch, MX123 Header, 80 Circuits Shrouded Assembly, Qty(80) 0.64mm Square Signal Pins, Harness Side Key Code G, Blue (Ag Mate Side Finish)
Application	Automotive, Power, Wire-to-Board
Component Type	PCB Header
Product Name	MX123
UPC	883906178659

Electrical

Current - Maximum per Contact	11.0A
Voltage - Maximum	500V

Physical

Breakaway	No
Circuits (Loaded)	80
Circuits (maximum)	80
Color - Resin	Blue
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Plating Mating	Silver
Material - Plating Termination	Tin
Net Weight	23.585/g
Number of Rows	4
Orientation	Vertical
Packaging Type	Carton
PCB Locator	No
PCB Retention	No
PC Tail Length	6.50mm
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	2.54mm
Polarized to Mating Part	Yes
Polarized to PCB	No
Shrouded	Shrouded
Stackable	No
Temperature Range - Operating	-40° to +125°C
Termination Interface Style	Through Hole

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Mates With / Use With

Mates with Part(s)

Description	Part Number
MX123 Receptacle Housings	<u>34566</u>

Use with Part(s)

Description	Part Number
MX64 Female Terminals	<u>34736</u>

This document was generated on Apr 30, 2026