


## Eurostrips®



Compact, easy to use double-row tubular screw terminal strips are a safe, cost effective alternative to barrier strips. Ideal for HVAC, appliance, power distribution and more. Dead front design. Supplied with wire protector. White polyamide 6.6

housing. Strips are easily cut to the desired number of poles.

### TS1.5 Flat Base

300 V, 15 A, 20-14 AWG. Pole Spacing: 8 mm (0.32"). Mounting Hole Diameter: 2.8 mm (0.11"). Width: 18.2 mm (0.72").

| Stock No. | Mfr.'s Type | Part No. | No. of Poles | Length mm (In.) | EACH |         |
|-----------|-------------|----------|--------------|-----------------|------|---------|
|           |             |          |              |                 | 1-99 | 100-499 |
| 502-1402  | TS1.5/2WP   | 40.002   | 2            | 13.6 (0.53)     | .50  | .39     |
| 502-1403  | TS1.5/3WP   | 40.003   | 3            | 21.5 (0.85)     | .75  | .61     |
| 502-1404  | TS1.5/4WP   | 40.004   | 4            | 29.5 (1.16)     | 1.00 | .79     |
| 502-1405  | TS1.5/5WP   | 40.005   | 5            | 37.4 (1.47)     | 1.24 | .98     |
| 502-1406  | TS1.5/6WP   | 40.006   | 6            | 45.4 (1.79)     | 1.50 | 1.19    |
| 502-1407  | TS1.5/7WP   | 40.007   | 7            | 53.3 (2.10)     | 1.75 | 1.37    |
| 502-1408  | TS1.5/8WP   | 40.008   | 8            | 61.3 (2.41)     | 2.00 | 1.60    |
| 502-1409  | TS1.5/9WP   | 40.009   | 9            | 69.2 (2.72)     | 2.24 | 1.78    |
| 502-1410  | TS1.5/10WP  | 40.010   | 10           | 77.2 (3.04)     | 2.45 | 1.98    |
| 502-1411  | TS1.5/11WP  | 40.011   | 11           | 85.1 (3.35)     | 2.69 | 2.17    |
| 502-1412  | TS1.5/12WP  | 40.012   | 12           | 93.0 (3.66)     | 2.69 | 2.17    |

### TS6 Flat Base (Continued)

300 V, 40 A, 18-10 AWG. Pole Spacing: 12 mm (0.47"). Mounting Hole Diameter: 4.2 mm (0.17"). Width: 23 mm (0.91").

| Stock No. | Mfr.'s Type | Part No. | No. of Poles | Length mm (In.) | EACH |         |
|-----------|-------------|----------|--------------|-----------------|------|---------|
|           |             |          |              |                 | 1-99 | 100-499 |
| 502-1445  | TS6/5WP     | 40.405   | 5            | 56.0 (2.21)     | 1.69 | 1.34    |
| 502-1446  | TS6/6WP     | 40.406   | 6            | 68.0 (2.68)     | 2.02 | 1.60    |
| 502-1447  | TS6/7WP     | 40.407   | 7            | 80.0 (3.15)     | 2.32 | 1.88    |
| 502-1448  | TS6/8WP     | 40.408   | 8            | 92.0 (3.62)     | 2.66 | 2.14    |
| 502-1449  | TS6/9WP     | 40.409   | 9            | 104.0 (4.10)    | 2.98 | 2.40    |
| 502-1450  | TS6/10WP    | 40.410   | 10           | 116.0 (4.57)    | 3.31 | 2.67    |
| 502-1451  | TS6/11WP    | 40.411   | 11           | 128.0 (5.04)    | 3.65 | 2.95    |
| 502-1452  | TS6/12WP    | 40.412   | 12           | 140.0 (5.51)    | 3.65 | 2.95    |

### TS2.5 Flat Base

300 V, 30 A, 18-12 AWG. Pole Spacing: 10 mm (0.39"). Mounting Hole Diameter: 3.5 mm (1.4"). Width: 22.3 mm (0.88").

| Stock No. | Mfr.'s Type | Part No. | No. of Poles | Length mm (In.) | EACH |         |
|-----------|-------------|----------|--------------|-----------------|------|---------|
|           |             |          |              |                 | 1-99 | 100-499 |
| 502-1422  | TS2.5/2WP   | 40.202   | 2            | 17.0 (0.67)     | .52  | .40     |
| 502-1423  | TS2.5/3WP   | 40.203   | 3            | 27.0 (1.06)     | .77  | .62     |
| 502-1424  | TS2.5/4WP   | 40.204   | 4            | 37.0 (1.46)     | 1.02 | .81     |
| 502-1425  | TS2.5/5WP   | 40.205   | 5            | 47.0 (1.85)     | 1.28 | 1.02    |
| 502-1426  | TS2.5/6WP   | 40.206   | 6            | 57.0 (2.24)     | 1.54 | 1.22    |
| 502-1427  | TS2.5/7WP   | 40.207   | 7            | 67.0 (2.64)     | 1.79 | 1.42    |
| 502-1428  | TS2.5/8WP   | 40.208   | 8            | 77.0 (3.03)     | 2.05 | 1.62    |
| 502-1429  | TS2.5/9WP   | 40.209   | 9            | 87.0 (3.43)     | 2.30 | 1.82    |
| 502-1430  | TS2.5/10WP  | 40.210   | 10           | 97.0 (3.82)     | 2.51 | 2.03    |
| 502-1431  | TS2.5/11WP  | 40.211   | 11           | 107.0 (4.21)    | 2.76 | 2.23    |
| 502-1432  | TS2.5/12WP  | 40.212   | 12           | 117.0 (4.61)    | 2.76 | 2.23    |

### TSF6 Standoff Feet

600 V, 30 A, 18-10 AWG. Pole Spacing: 12 mm (0.47"). Mounting Hole Diameter: 4.2 mm (0.16"). Width: 23.0 mm (0.91").


| Stock No. | Mfr.'s Type | Part No. | No. of Poles | Length mm (In.) | EACH |         |
|-----------|-------------|----------|--------------|-----------------|------|---------|
|           |             |          |              |                 | 1-99 | 100-499 |
| 502-1482  | TSF6/2WP    | 40.502   | 2            | 20.0 (0.79)     | .69  | .54     |
| 502-1483  | TSF6/3WP    | 40.503   | 3            | 32.0 (1.26)     | 1.05 | .83     |
| 502-1484  | TSF6/4WP    | 40.504   | 4            | 44.0 (1.73)     | 1.39 | 1.10    |
| 502-1485  | TSF6/5WP    | 40.505   | 5            | 56.0 (2.20)     | 1.75 | 1.37    |
| 502-1486  | TSF6/6WP    | 40.506   | 6            | 68.0 (2.68)     | 2.09 | 1.66    |
| 502-1487  | TSF6/7WP    | 40.507   | 7            | 80.0 (3.15)     | 2.44 | 1.93    |
| 502-1488  | TSF6/8WP    | 40.508   | 8            | 92.0 (3.62)     | 2.74 | 2.20    |
| 502-1489  | TSF6/9WP    | 40.509   | 9            | 104.0 (4.10)    | 3.07 | 2.47    |
| 502-1490  | TSF6/10WP   | 40.510   | 10           | 116.0 (4.57)    | 3.42 | 2.77    |
| 502-1491  | TSF6/11WP   | 40.511   | 11           | 128.0 (5.04)    | 3.77 | 3.04    |
| 502-1492  | TSF6/12WP   | 40.512   | 12           | 140.0 (5.51)    | 3.77 | 3.04    |

### TSF16 Standoff Feet

600 V, 63 A, 14-6 AWG. Pole Spacing: 15 mm (0.59"). Mounting Hole Diameter: 4 mm (0.16"). Width: 26.5 mm (1.04").

| Stock No. | Mfr.'s Type | Part No. | No. of Poles | Length mm (In.) | EACH |         |
|-----------|-------------|----------|--------------|-----------------|------|---------|
|           |             |          |              |                 | 1-99 | 100-499 |
| 502-1533  | TSF16/2WP   | 40.702   | 2            | 25.0 (0.98)     | 1.66 | 1.31    |
| 502-1535  | TSF16/3WP   | 40.703   | 3            | 40.0 (1.58)     | 2.48 | 1.97    |
| 502-1537  | TSF16/4WP   | 40.704   | 4            | 55.0 (2.17)     | 3.25 | 2.61    |
| 502-1541  | TSF16/5WP   | 40.705   | 5            | 70.5 (2.28)     | 4.07 | 3.28    |
| 502-1539  | TSF16/9WP   | 40.709   | 9            | 131.0 (5.16)    | 7.18 | 5.90    |
| 502-1542  | TSF16/12WP  | 40.712   | 12           | 176.0 (6.93)    | 8.78 | 7.21    |

## Panel Mount Terminal Blocks



- High Density, Terminations Per Foot
- Screw-Cage Clamp

- Accepts Standard Marking Tags

Compact and convenient to use where space is a constraint. Cost effective sectional design allows for changing requirements. Order preassembled or easily snap together single pole components to form multipole assemblies. Mounting sections snap onto ends of assembly or between terminal block components to provide additional mounting points.

CMB4 assemblies feature an internal bussing provision to distribute power selectively or throughout the assembly.

### CMB4 Terminal Block Components (1 Pole) and Assemblies (2 Poles and Up)

300 V, 20 A, 22-10 AWG. Pole Spacing: 6 mm (0.236"). 27 mm (1.06") wide x 23 mm (0.91") high.

| Stock No. | Mfr.'s Type | No. of Poles | Length mm (In.) | EACH  |         |
|-----------|-------------|--------------|-----------------|-------|---------|
|           |             |              |                 | 1-99  | 100-499 |
| 502-3714  | CMB4        | 1*           | 6.0 (0.236)     | .93   | .72     |
| 502-3716  | CMB4/2      | 2            | 26.5 (1.040)    | 3.01  | 2.39    |
| 502-3718  | CMB4/3      | 3            | 32.6 (1.280)    | 3.96  | 3.15    |
| 502-3720  | CMB4/4      | 4            | 38.7 (1.520)    | 4.93  | 3.91    |
| 502-3722  | CMB4/5      | 5            | 44.8 (1.760)    | 5.89  | 4.68    |
| 502-3724  | CMB4/6      | 6            | 50.9 (2.000)    | 6.83  | 5.44    |
| 502-3726  | CMB4/7      | 7            | 57.0 (2.240)    | 7.81  | 6.21    |
| 502-3728  | CMB4/8      | 8            | 63.1 (2.480)    | 8.76  | 6.96    |
| 502-3730  | CMB4/9      | 9            | 69.2 (2.720)    | 9.71  | 7.72    |
| 502-3732  | CMB4/10     | 10           | 75.3 (2.960)    | 10.68 | 8.50    |
| 502-3734  | CMB4/11     | 11           | 81.4 (3.200)    | 11.64 | 9.27    |
| 502-3736  | CMB4/12     | 12           | 87.5 (3.440)    | 12.58 | 10.03   |

### Mounting Section for CMB4 Components

| Stock No. | Mfr.'s Type | No. of Poles | Length mm (In.) | EACH    |
|-----------|-------------|--------------|-----------------|---------|
| 502-3738  | EPCMB4      | —            | —               | .51 .40 |

\*Order mounting sections separately.

Note: For individual jumpers, contact your local Allied sales representative.

## High Temperature Ceramic Euroblock™

- Compact, Space Saving
- Tubular Screw Clamp
- Free Float or Panel Mount
- Temperature Range: -20°C to 800°C (-4°F to 1472°F)
- Standard Color: Beige
- Housing: Steatite
- Clamp: Brass
- Screws: Zinc Plated Steel

Suitable for use in high temperature applications up to 800°C (1472°F). Applications include hot melt glue guns, furnaces, heaters, process equipment and machinery. Terminal blocks are offered with mounting holes for panel mounting or free floating applications.

| Stock No. | Mfr.'s Type | No. of Poles | Amps | Volts | Wire Size |     | Dimensions mm |                |                |                |      |   |      |      | EACH |         |
|-----------|-------------|--------------|------|-------|-----------|-----|---------------|----------------|----------------|----------------|------|---|------|------|------|---------|
|           |             |              |      |       | mm        | AWG | A             | B <sub>1</sub> | B <sub>2</sub> | B <sub>3</sub> | C    | D | E    | F    | 1-99 | 100-499 |
| 502-7300  | E71         | 1            | 32 A | 450 V | 4.0       | 12  | 25.0          | 10             | 22             | 34             | 10.5 | 4 | 18.5 | 3.25 | .46  | .40     |
| 502-7302  | E72         | 2            | 32 A | 450 V | 4.0       | 12  | 25.0          | 10             | 22             | 34             | 10.5 | 4 | 18.5 | 3.25 | .75  | .65     |
| 502-7304  | E73         | 3            | 32 A | 450 V | 4.0       | 12  | 25.0          | 10             | 22             | 34             | 10.5 | 4 | 18.5 | 3.25 | .98  | .83     |
| 502-7306  | E81         | 1            | 41 A | 450 V | 6.0       | 10  | 26.0          | 11             | 24             | 37             | 10.5 | 4 | 20.5 | 4.10 | .64  | .54     |
| 502-7308  | E82         | 2            | 41 A | 450 V | 6.0       | 10  | 26.0          | 11             | 24             | 37             | 10.5 | 4 | 20.5 | 4.10 | .93  | .77     |
| 502-7310  | E83         | 3            | 41 A | 450 V | 6.0       | 10  | 26.0          | 11             | 24             | 37             | 10.5 | 4 | 20.5 | 4.10 | 1.37 | 1.19    |
| 502-7312  | E91         | 1            | 76 A | 450 V | 16.0      | 6   | 32.4          | 15             | 30             | 45             | 13.0 | 4 | 23.0 | 5.60 | .77  | .67     |
| 502-7314  | E92         | 2            | 76 A | 450 V | 16.0      | 6   | 32.4          | 15             | 30             | 45             | 13.0 | 4 | 23.0 | 5.60 | 1.27 | 1.06    |
| 502-7316  | E93         | 3            | 76 A | 450 V | 16.0      | 6   | 32.4          | 15             | 30             | 45             | 13.0 | 4 | 23.0 | 5.60 | 1.59 | 1.37    |

