



Pushing Performance  
Since 1945

# Han Q 17/0-F-c 10A



Image is for illustration purposes only. Please refer to product description.

Part number	09 12 017 3101
Specification	Han Q 17/0-F-c 10A
HARTING eCatalogue	<a href="https://b2b.harting.com/09120173101">https://b2b.harting.com/09120173101</a>

## Identification

Category	Inserts
Series	Han <sup>®</sup> Q
Identification	17/0

## Version

Termination method	Crimp termination
Gender	Female
Size	Han-Compact <sup>®</sup>
Number of contacts	17
PE contact	Yes
Details	Please order crimp contacts separately.

## Technical characteristics

Conductor cross-section	0.14 ... 2.5 mm <sup>2</sup>
Rated current	10 A
Rated voltage	160 V
Rated impulse voltage	2.5 kV
Pollution degree	3
Rated voltage acc. to UL	250 V
Rated voltage acc. to CSA	250 V
Insulation resistance	>10 <sup>10</sup> Ω
Limiting temperature	-40 ... +125 °C



Pushing Performance  
Since 1945

Technical characteristics

Mating cycles	≥500
---------------	------

Material properties

Material (insert)	Polycarbonate (PC)
Colour (insert)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3)
	R23 (HL 1-3)

Specifications and approvals

Specifications	IEC 60664-1
	IEC 61984
UL / CSA	UL 1977 ECBT2.E235076
	CSA-C22.2 No. 182.3 ECBT8.E235076
Approvals	DNV GL

Commercial data

Packaging size	10
Net weight	9.58 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140018112
ETIM	EC000438
eCl@ss	27440205 Contact insert for industrial connectors