




Color: ■ gray



Dimensions in mm
L = 12.8 mm



PCB terminal block, 2616 Series, 0 °conductor entry to board

This PCB terminal block (item number 2616-1101) is designed for quick and simple connections. You can count on tried and tested safety with these PCB terminal blocks, perfect for a wide variety of applications when designing your devices. This PCB terminal block has a rated voltage of 1000 V and can handle currents up to 76 A, making it ideal for high-load applications. Strip lengths must be between 18 mm and 20 mm when connecting conductors to this PCB terminal block. Featuring one conductor terminal along with Push-in CAGE CLAMP®, this product outperforms the competition. Push-in CAGE CLAMP® technology provides a universal connection solution for all conductor types. It allows both solid and fine-stranded conductors with ferules to be inserted directly into the clamping point without the need for tools. Dimensions: 12.8 x 37.2 x 32 mm (width x height x depth). Depending on the conductor type, this PCB terminal block is ideal for conductor cross sections ranging from 0.75 mm² to 16 mm². Up to one potential / one pole can be connected to this terminal block using one clamping point on one level. The gray housing is made of polyamide (PA66) for insulation, the contacts are made of electrolytic copper (ECu), and the clamping spring is made of chrome-nickel spring steel (CrNi). The contact surface is coated with tin. A lever is used to operate this PCB terminal block. THT is used to solder the PCB terminal block. Insert the conductor at a 0° angle.. The solder pins measure 1.2 x 1.2 mm in cross-section and 4 mm in length and are arranged over the entire terminal strip (in-line). There are six solder pins per potential.

| Notes | |
|-----------|--|
| Note | The inherent stability of a single-pole PCB terminal block is less than that of a multi-pole terminal strip. The customer must therefore ensure that these terminal blocks are protected against excessive mechanical stress (e.g., torsional or bending stress), both when connecting the conductor and during subsequent use, for example by providing additional support, shortly holding the connected conductor and appropriate actuation instructions. |
| Variants: | Other pole numbers Direct marking Other colors Other versions (or variants) can be requested from WAGO Sales or configured at https://configurator.wago.com/ . |



| Electrical data | | | | | | |
|----------------------|--------|----------------|--------|---------------|---------------|-------|
| Ratings per | | IEC/EN 60664-1 | | | Approvals per | |
| | | UL 1059 | | | | |
| Overvoltage category | III | III | II | Use group | B | C |
| Pollution degree | 3 | 2 | 2 | Rated voltage | 600 V | 600 V |
| Nominal voltage | 1000 V | 1000 V | 1000 V | Rated current | 78 A | 78 A |
| Rated surge voltage | 8 kV | 8 kV | 8 kV | | | |
| Rated current | 76 A | 76 A | 76 A | | | |

| Approvals per | | CSA | | |
|---------------|-------|--------|---|--|
| Use group | B | C | D | |
| Rated voltage | 600 V | 1000 V | - | |
| Rated current | 72 A | 72 A | - | |

| Connection data | | | |
|----------------------------|---|---|-------------------------------------|
| Clamping units | 1 | Connection 1 | |
| Total number of potentials | 1 | Connection technology | Push-in CAGE CLAMP® |
| Number of connection types | 1 | Actuation type | Lever |
| Number of levels | 1 | Solid conductor | 0.75 ... 16 mm² / 18 ... 4 AWG |
| | | Fine-stranded conductor | 0.75 ... 25 mm² / 18 ... 4 AWG |
| | | Fine-stranded conductor; with insulated ferrule | 0.75 ... 16 mm² |
| | | Fine-stranded conductor; with uninsulated ferrule | 0.75 ... 16 mm² |
| | | Fine-stranded conductor; with twin ferrule | 0.75 ... 6 mm² |
| | | Strip length | 18 ... 20 mm / 0.71 ... 0.79 inches |
| | | Conductor connection direction to PCB | 0° |
| | | Pole number | 1 |

| Physical data | |
|--------------------------------------|------------------------|
| Pin spacing | 10 mm / 0.394 inches |
| Width | 12.8 mm / 0.504 inches |
| Height | 37.2 mm / 1.465 inches |
| Height from the surface | 33.2 mm / 1.307 inches |
| Depth | 32 mm / 1.26 inches |
| Solder pin length | 4 mm |
| Solder pin dimensions | 1.2 x 1.2 mm |
| Drilled hole diameter with tolerance | 1.7 (+0.1) mm |

| PCB contact | |
|-------------------------------------|--|
| PCB contact | THT |
| Solder pin arrangement | over the entire terminal strip (in-line) |
| Number of solder pins per potential | 6 |



| Material data | |
|------------------------------------|--|
| Note (material data) | Information on material specifications can be found here |
| Color | gray |
| Material group | I |
| Insulation material (main housing) | Polyamide (PA66) |
| Flammability class per UL94 | V0 |
| Clamping spring material | Chrome-nickel spring steel (CrNi) |
| Contact material | Electrolytic copper (E _{Cu}) |
| Contact Plating | Tin |
| Fire load | 0.176 MJ |
| Actuator color | orange |
| Weight | 10.8 g |






| Environmental requirements | |
|----------------------------|-----------------|
| Limit temperature range | -60 ... +105 °C |
| Processing temperature | -35 ... +60 °C |

| Commercial data | |
|-----------------------|---------------|
| PU (SPU) | 100 pcs |
| Packaging type | Box |
| Country of origin | PL |
| GTIN | 4055143692762 |
| Customs tariff number | 85369010000 |

| Product Classification | |
|------------------------|----------------------|
| UNSPSC | 39121409 |
| eCl@ss 10.0 | 27-44-04-01 |
| eCl@ss 9.0 | 27-44-04-01 |
| ETIM 9.0 | EC002643 |
| ETIM 8.0 | EC002643 |
| ECCN | NO US CLASSIFICATION |

| Environmental Product Compliance | |
|----------------------------------|-------------------------|
| RoHS Compliance Status | Compliant, No Exemption |

Approvals / Certificates

| General approvals | | | Declarations of conformity and manufacturer's declarations | | |
|--|---------------|-------------------------------------|---|----------|------------------|
|     | | |  | | |
| Approval | Standard | Certificate Name | Approval | Standard | Certificate Name |
| CSA DEKRA Certification B.V. | C22.2 | 70154737 | Railway WAGO GmbH & Co. KG | - | Z00004414.000 |
| DEKRA DEKRA Certification B.V. | EN 60947-7-4 | 71-148282 | | | |
| KEMA/KEUR DEKRA Certification B.V. | EN 60947-7-4 | 71-110774 | | | |
| UL Underwriters Laboratories Inc. | C22.2 No. 158 | UL-US- L45172-6187173-60217102-1 | | | |

Downloads

Environmental Product Compliance

Compliance Search

Environmental Product Compliance 2616-1101

↓

Documentation

Additional Information

Technical Section

03.04.2019

pdf

2027.26 KB

↓

CAD/CAE-Data

CAD data

2D/3D Models 2616-1101

↓

CAE data

ZUKEN Portal 2616-1101

↓

PCB Design

Symbol and Footprint via SamacSys 2616-1101

↓

Symbol and Footprint via Ultra Librarian 2616-1101

↓

1 Compatible Products

1.1 Optional Accessories


1.1.1 Ferrule

1.1.1.1 Ferrule



[Item No.: 216-284](#)
Ferrule; Sleeve for 1.5 mm² / AWG 16; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; black





[Item No.: 216-289](#)
Ferrule; Sleeve for 10 mm² / AWG 8; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; red





[Item No.: 216-210](#)
Ferrule; Sleeve for 16 mm² / AWG 6; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; blue





[Item No.: 216-286](#)
Ferrule; Sleeve for 2.5 mm² / AWG 14; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; blue





[Item No.: 216-287](#)
Ferrule; Sleeve for 4 mm² / AWG 12; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; gray






[Item No.: 216-288](#)
Ferrule; Sleeve for 6 mm² / AWG 10; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; yellow




Installation Notes

Conductor termination



Insert fine-stranded conductors – and remove all conductors – via operating tool.

Conductor termination



Insert solid conductors via push-in termination.