Part Number : 1203410945
Product Description : Micro-Change (M12) CAT6A Double-Ended Cordset, 8 Poles, X-Coded, Male (Straight) to Male (Straight), 26 AWG, Green Teal Shielded TPE Cable, 23.0m (75.46') Length
Series Number : 120341
Status : Active
Product Category : Industrial Cable Assemblies
Engineering Part Number : E22E06021M230



Documents and Resources

Drawings

1203410945_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Contains Lead; 6,6'-Di-tert-butyl-2,2'-methylenedi-p-cresol per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Downloaded from Arrow.com.

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Industrial Cable Assemblies
Series	120341
Description	Micro-Change (M12) CAT6A Double-Ended Cordset, 8 Poles, X-Coded, Male (Straight) to Male (Straight), 26 AWG, Green Teal Shielded TPE Cable, 23.0m (75.46') Length
IP Rating	IP67
Performance Category	6A
Product Name	Micro-Change (M12) Cat6A,Industrial Ethernet
Protocol	EtherNet
Type	Double Ended
UPC	195842024694

Agency

UL	E361772

Electrical

Current - Maximum per Contact	0.5A
Voltage - Maximum	48V

Physical

Cable Diameter	7.30mm (.287")
Cable Length	23.0m (75.46')
Color - Cable Jacket	Green Teal
Connector End A	Micro-Change (M12)

Downloaded from Arrow.com.

Connector End B	Micro-Change (M12)
Coupling Style	Threaded
Gender	Male-Male
Keyway	X-Coded
LED Indicator	None
Material - Cable Jacket	TPE
Material - Connector Body	TPU
Material - Contact	Brass
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold
Net Weight	40.940/g
Orientation	Straight to Straight
Poles	8
Temperature Range - Operating	-25° to +80°C
Wire/Cable Type	Shielded TPE
Wire Size (AWG)	26

Downloaded from Arrow.com.