


39512500440 - 395 Series



Series: 395

Fuse 395 Datasheet

- Features:
- Reduced PCB space requirements
 - Direct solderable or plug-in versions
 - Internationally approved
 - Low internal resistance
 - Shocksafe casing
 - Vibration resistant
 - Halogen free
 - CCCe for China import

Click on part number below for individual TC curve files.

Questions? [Contact Littelfuse Support](#)

Check Stock

Order Samples

Feedback

Electrical Characteristics		Technical Resources		Environmental Info	
Property (Mouseover for details)				Value	
Ampere Rating (A)				2.5	
Nominal Melting I²T (A²sec)				1.1	
Interrupting Rating				100A@125VAC	
Min Operating Temp °C				-40	
Max Operating Temp (°C)				85	
Moisture Sensitivity Level				MIL-STD-202 Method 106	
Nominal Power Dissipation (W)				375	
Nominal Voltage Drop (mV)				150	
Nominal Cold Resistance (Ohms)				0.03048	
Opening				Fast-Acting (F)	
Package Size				TE5 (8.5x8mm)	
VAC (V)				125	

Connect with Littelfuse

Sign up to receive special offers and news

Enter your email

Submit

For more details about how we use your information, check our [Privacy Statement](#).

Mobile Site

- About Littelfuse
- About Littelfuse
 - Conflict Free Statement
 - History
 - Investor Relations
 - Legal
 - Press Room
 - Privacy Statement
 - Supply Chain Transparency
 - Website Feedback

- Explore Littelfuse
- Capabilities Brochures
 - Careers
 - Check Distributor Stock
 - Competitor Cross Reference
 - Industries
 - Order Samples
 - Products
 - Services

- Technical Resources
- Application Designs
 - Education
 - FAQs
 - iDesign™
 - Littelfuse University
 - Product Catalogs
 - Quality Documents
 - Technical Documents