ON Semiconductor

Is Now



To learn more about onsemi™, please visit our website at
www.onsemi.com

onsemi and onsemi and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi** product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner. Other names and brands may be claimed as the property of others.

Downloaded from Arrow.com.

ECH8693R

Power MOSFET
for 1-2 Cells Lithium-ion Battery Protection
24 V, 7 mΩ, 14 A, Dual N-Channel

ON Semiconductor®

www.onsemi.com


This Power MOSFET features a low on-state resistance. This device is suitable for applications such as power switches of portable machines. Best suited for 1-2 cells Lithium-ion Battery applications.

V_{DSS}	R_{DS}(on) Max	I_D Max
24 V	7 mΩ @ 4.5 V	14 A
	7.5 mΩ @ 4.0 V	
	9.1 mΩ @ 3.1 V	
	10.5 mΩ @ 2.5 V	

Features
- Low On-Resistance
- 2.5 V drive
- Common-Drain Type
- ESD Diode-Protected Gate
- Built-in Gate Protection Resistor
- Pb-Free, Halogen Free and RoHS compliance

Typical Applications
- 1-2 cells Lithium-ion Battery Charging and Discharging Switch

ELECTRICAL CONNECTION
N-Channel




1 : Source1
2 : Gate1
3 : Source2
4 : Gate2
5 : Drain
6 : Drain
7 : Drain
8 : Drain

SPECIFICATIONS
ABSOLUTE MAXIMUM RATING at Ta = 25°C (Note 1)


Parameter	Symbol	Value	Unit
Drain to Source Voltage	V_{DSS}	24	V
Gate to Source Voltage	V_{GSS}	±12.5	V
Drain Current (DC)	I_D	14	A
Drain Current (Pulse) PW ≤ 10 μs, duty cycle ≤ 1%	I_{DP}	60	A
Power Dissipation Surface mounted on ceramic substrate (900 mm^2 × 0.8 mm) 1 unit	P_D	1.4	W
Total Dissipation Surface mounted on ceramic substrate (900 mm^2 × 0.8 mm)	P_T	1.5	W
Junction Temperature	Tj	150	°C
Storage Temperature	Tstg	−55 to +150	°C

Note 1 : Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

MARKING



SOT-28FL / ECH8



THERMAL RESISTANCE RATINGS

Parameter	Symbol	Value	Unit
Junction to Ambient Surface mounted on ceramic substrate (900 mm^2 × 0.8 mm) 1 unit	$R_{\theta JA}$	89.2	°C/W

ORDERING INFORMATION
See detailed ordering and shipping information on page 5 of this data sheet.

© Semiconductor Components Industries, LLC, 2016

Downloaded from Arrow.com.

ELECTRICAL CHARACTERISTICS at Ta = 25°C (Note 2)

Parameter	Symbol	Conditions	Value			Unit
			min	typ	max	
Drain to Source Breakdown Voltage	$V_{(BR)DSS}$	I_D = 1 mA, V_{GS} = 0 V	24			V
Zero-Gate Voltage Drain Current	I_{DSS}	V_{DS} = 20 V, V_{GS} = 0 V			1	μA
Gate to Source Leakage Current	I_{GSS}	V_{GS} = ±8 V, V_{DS} = 0 V			±1	μA
Gate Threshold Voltage	$V_{GS}(th)$	V_{DS} = 10 V, I_D = 1 mA	0.5		1.3	V
Forward Transconductance	g_{FS}	V_{DS} = 10 V, I_D = 5 A		8		S
Static Drain to Source On-State Resistance	$R_{DS}(on)$	I_D = 5 A, V_{GS} = 4.5 V	4.4	5.6	7	mΩ
		I_D = 5 A, V_{GS} = 4.0 V	4.6	5.8	7.5	mΩ
		I_D = 5 A, V_{GS} = 3.1 V	5.2	6.5	9.1	mΩ
		I_D = 2.5 A, V_{GS} = 2.5 V	6	7.5	10.5	mΩ
Turn-ON Delay Time	$t_d(on)$	See Fig. 1 (Note 3)		545		ns
Rise Time	t_r			525		ns
Turn-OFF Delay Time	$t_d(off)$			18.65		μs
Fall Time	t_f			22.2		μs
Turn-ON Delay Time	$t_d(on)$	See Fig. 2 (Note 3)		545		ns
Rise Time	t_r			525		ns
Turn-OFF Delay Time	$t_d(off)$			1,130		μs
Fall Time	t_f			410		μs
Total Gate Charge	Qg	V_{DS} = 10 V, V_{GS} = 4.5 V, I_D = 14 A		13		nC
Gate to Source Charge	Qgs			3		nC
Gate to Drain “Miller” Charge	Qgd			2.4		nC
Forward Diode Voltage	V_{SD}	I_S = 14 A, V_{GS} = 0 V		0.78	1.2	V

Note 2 : Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

Note 3 : The fall switching time is dependent on the input pulse width.

Fig.1 Switching Time Test Circuit 1








Fig.2 Switching Time Test Circuit 2





Downloaded from Arrow.com.























Downloaded from Arrow.com.








Downloaded from Arrow.com.

PACKAGE DIMENSIONS


unit : mm

SOT-28FL / ECH8
CASE 318BF
ISSUE O



1 : Source1
2 : Gate1
3 : Source2
4 : Gate2
5 : Drain
6 : Drain
7 : Drain
8 : Drain

Recommended Soldering Footprint



ORDERING INFORMATION

Device	Marking	Package	Shipping (Qty / Packing)
ECH8693R-TL-W	UQ	SOT-28FL / ECH8 (Pb-Free / Halogen Free)	3,000 / Tape & Reel

† For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D. http://www.onsemi.com/pub_link/Collateral/BRD8011-D.PDF

Note on usage : Since the ECH8693R is a MOSFET product, please avoid using this device in the vicinity of highly charged objects. Please contact sales for use except the designated application.

ON Semiconductor and the ON Semiconductor logo are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconductor was negligent regarding the design or manufacture of the part. ON Semiconductor is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

Downloaded from Arrow.com.