

NAVIGATE THE CATALOG BY SECTIONS

1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22
---	---	---	---	---	---	---	---	---	----	----	----	----	----	----	----	----	----	----	----	----	----

6

6


Strain Relief Cord Connectors

SKINTOP® SL/SLR

Liquid Tight, Non -Metallic Strain Relief Cable Gland with PG Threads

SKINTOP® SL/ SLR is a durable, liquid tight, easy to assemble strain relief cable gland with PG threads that is universally suited for all types of machinery & equipment, including automation, motion control, process control and robotics.

- Application Advantage:**
- The heavy duty SKINTOP® design provides great pullout strength and very reliable strain relief
 - Superior integrated locking mechanism includes an internal ratchet for vibration proof protection
 - Multi-trapezoidal thread requires just one twist to tighten
 - Generous high quality neoprene bushing provides a liquid tight and dust proof, hermetic seal



Technical Data:	
	Materials:
	Body: Polyamide
	Bushing: CR
	Locknuts: Included
	Color:
	Black (RAL 9005) UV Resistant
	Gray (RAL 7001)
	* Lt Gray (RAL 7035) available upon request
	Protection Seal:
	70 PSI
	IP 68, 5 Bar
	Exceeds NEMA 6/6P Pressure rating
	Temperature Range:
	-20°C to +80°C
	Static: -40°C to +80°C
	Dynamic: -20°C to +80°C

DOWNLOAD PDF CATALOG PAGE

SAMPLE REQUEST

AUTOCAD

Find Mating Parts for your cable

Need an EPIC® Connector?

Need a SKINTOP® Strain Relief?

Enter your Cable Part #

Find Mating Parts

Part Number	Thread Type	UL Status	Clamping Range ? F inches	SW Wrenching Flats inches	C Overall Length inches	D Thread Length inches	Standard Pack Size	Weight 100 pcs. lbs.
PG Thread - Standard Type - Black								
S2107	PG- 7	R	.098 - .256	0.591	1.260	0.315	100	1.00
S2109	PG- 9	R	.138 - .315	0.748	1.417	0.315	100	1.50
S2111	PG- 11	R	.157 - .394	0.866	1.496	0.315	100	2.00
S2113	PG- 13	L	.236 - .472	0.945	1.614	0.354	100	2.50
S2116	PG- 16	L	.354 - .551	1.063	1.732	0.394	50	3.00
S2121	PG- 21	L	.512 - .709	1.299	1.929	0.433	50	5.00
S2129	PG- 29	R	.551 - .984	1.654	2.205	0.433	25	8.50
S2136	PG- 36	L	.945 - 1.260	2.087	2.598	0.512	10	17.50
S2142	PG- 42	R	1.378 - 1.496	2.362	2.677	0.512	5	24.00
S2148	PG- 48	L	1.535 - 1.732	2.559	2.717	0.551	5	29.00
PG Thread - Standard Type - Gray								
S1107	PG- 7	R	.098 - .256	0.591	1.260	0.315	100	1.00
S1109	PG- 9	R	.138 - .315	0.748	1.417	0.315	100	1.50
S1111	PG- 11	R	.157 - .394	0.866	1.496	0.315	100	2.00
S1113	PG- 13	L	.236 - .472	0.945	1.614	0.354	100	2.50
S1116	PG- 16	L	.354 - .551	1.063	1.732	0.394	50	3.00
S1121	PG- 21	L	.512 - .709	1.299	1.929	0.433	50	5.00
S1129	PG- 29	R	.551 - .984	1.654	2.205	0.433	25	8.50
S1136	PG- 36	L	.945 - 1.260	2.087	2.598	0.512	10	17.50
S1142	PG- 42	R	1.378 - 1.496	2.362	2.677	0.512	5	24.00
S1148	PG- 48	L	1.535 - 1.732	2.559	2.717	0.551	5	29.00
PG Thread with Reducer Bushing - Black								
S2207	PG- 7	R	.059 - .197	0.591	1.260	0.315	100	1.00
S2209	PG- 9	R	.079 - .236	0.748	1.417	0.315	100	1.50
S2211	PG- 11	R	.079 - .276	0.866	1.496	0.315	100	2.00
S2213	PG- 13	L	.157 - .354	0.945	1.614	0.354	100	2.50
S2216	PG- 16	L	.236 - .472	1.063	1.732	0.394	50	3.00
S2221	PG- 21	L	.354 - .630	1.299	1.929	0.433	50	5.00
S2229	PG- 29	R	.433 - .787	1.654	2.205	0.433	25	8.50
S2236	PG- 36	L	.669 - 1.024	2.087	2.598	0.512	10	17.50
S2242	PG- 42	R	.866 - 1.220	2.362	2.677	0.512	5	24.00
S2248	PG- 48	L	1.024 - 1.378	2.559	2.717	0.551	5	29.00
PG Thread with Reducer Bushing - Gray								
S1207	PG- 7	R	.059 - .197	0.591	1.260	0.315	100	1.00
S1209	PG- 9	R	.079 - .236	0.748	1.417	0.315	100	1.50
S1211	PG- 11	R	.079 - .276	0.866	1.496	0.315	100	2.00
S1213	PG- 13	L	.157 - .354	0.945	1.614	0.354	100	2.50
S1216	PG- 16	L	.236 - .472	1.063	1.732	0.394	50	3.00
S1221	PG- 21	L	.354 - .630	1.299	1.929	0.433	50	5.00
S1229	PG- 29	R	.433 - .787	1.654	2.205	0.433	25	8.50
S1236	PG- 36	L	.669 - 1.024	2.087	2.598	0.512	10	17.50
S1242	PG- 42	R	.866 - 1.220	2.362	2.677	0.512	5	24.00
S1248	PG- 48	L	1.024 - 1.378	2.559	2.717	0.551	5	29.00