



REV.	DATE	DESCRIPTION
B	04/31/03	UPDATE DRAWING FORMAT



NOTE:

1. CRIMPED FERRULE
HEX CRIMP SIZE .128"
2. CONTACT PIN TO SOLDER

					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020” DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex						
8						DRAWN	G.R.S.	04/31/03								
7						CHECKED										
6										PART DESCRIPTION						
5	FERRULE	COPPER	GOLD	1						MMCX R/A CRIMP PLUG (FOR RG–178B/U, 196A/U)						
4	COVER	BRASS	GOLD	1						PART NO.						
3	CONTACT PIN	BRASS	GOLD	1						262102						
2	INSULATOR	TEFLON	NATURAL	1						DWG. NO.						
1	BODY	BRASS	GOLD	1					262102.DWG							
	DESCRIPTION	MATERIAL	FINISH	QTY					CAD FILE		REV.	B	SIZE	A	SCALE	NA
									C:/262/262102.DWG							