

P-Channel Enhancement Mode Power MOSFET

Description


The G12P10KE uses advanced trench technology to provide excellent $R_{DS(ON)}$, low gate charge. It can be used in a wide variety of applications.

General Features


- V_{DS} -100V
- I_D (at $V_{GS} = -10V$) -12A
- $R_{DS(ON)}$ (at $V_{GS} = -10V$) < 200m Ω
- $R_{DS(ON)}$ (at $V_{GS} = -4.5V$) < 250m Ω
- 100% Avalanche Tested
- RoHS Compliant
- ESD (HBM) : 7.0KV

Application

- Power switch
- DC/DC converters



Schematic diagram



TO-252

Ordering Information

Device	Package	Marking	Packaging
G12P10KE	TO-252	G12P10	2500pcs/Reel

Absolute Maximum Ratings $T_C = 25^\circ\text{C}$, unless otherwise noted

Parameter	Symbol	Value	Unit
Drain-Source Voltage	V_{DS}	-100	V
Continuous Drain Current	I_D	$T_C = 25^\circ\text{C}$ -12	A
		$T_C = 100^\circ\text{C}$ -7.5	
Pulsed Drain Current (note1)	I_{DM}	-48	A
Gate-Source Voltage	V_{GS}	± 20	V
Power Dissipation	P_D	45	W
Single pulse avalanche energy (note2)	E_{AS}	25	mJ
Operating Junction and Storage Temperature Range	T_J, T_{stg}	-55 To 150	$^\circ\text{C}$

Thermal Resistance

Parameter	Symbol	Value	Unit
Thermal Resistance, Junction-to-Ambient	R_{thJA}	55	$^\circ\text{C/W}$
Thermal Resistance, Junction-to-Case	R_{thJC}	2.8	$^\circ\text{C/W}$

Specifications T _J = 25°C, unless otherwise noted						
Parameter	Symbol	Test Conditions	Value			Unit
			Min.	Typ.	Max.	
Static Parameters						
Drain-Source Breakdown Voltage	V _{(BR)DSS}	V _{GS} = 0V, I _D = -250μA	-100	--	--	V
Zero Gate Voltage Drain Current	I _{DSS}	V _{DS} = -100V, V _{GS} = 0V	--	--	-1	μA
Gate-Source Leakage	I _{GSS}	V _{GS} = ±20V	--	--	±10	uA
Gate-Source Threshold Voltage	V _{GS(th)}	V _{DS} = V _{GS} , I _D = -250μA	-1.0	-1.7	-3.0	V
Drain-Source On-Resistance	R _{DS(on)}	V _{GS} = -10V, I _D = -6A	--	178	200	mΩ
		V _{GS} = -4.5V, I _D = -6A	--	192	250	
Forward Transconductance	g _{FS}	V _{DS} = -15V, I _D = -6A	--	12	--	S
Dynamic Parameters						
Input Capacitance	C _{iss}	V _{GS} = 0V, V _{DS} = -50V, f = 1.0MHz	--	1700	--	pF
Output Capacitance	C _{oss}		--	50	--	
Reverse Transfer Capacitance	C _{rss}		--	45	--	
Total Gate Charge	Q _g	V _{DD} = -50V, I _D = -6A, V _{GS} = -10V	--	32	--	nC
Gate-Source Charge	Q _{gs}		--	5	--	
Gate-Drain Charge	Q _{gd}		--	7	--	
Turn-on Delay Time	t _{d(on)}	V _{DD} = -50V, I _D = -6A, R _G = 9Ω	--	52	--	ns
Turn-on Rise Time	t _r		--	12	--	
Turn-off Delay Time	t _{d(off)}		--	38	--	
Turn-off Fall Time	t _f		--	28	--	
Drain-Source Body Diode Characteristics						
Continuous Body Diode Current	I _S	T _C = 25°C	--	--	-12	A
Body Diode Voltage	V _{SD}	T _J = 25°C, I _{SD} = -6A, V _{GS} = 0V	--	--	-1.2	V
Reverse Recovery Charge	Q _{rr}	I _F = -6A, V _{GS} = 0V di/dt=-500A/us	--	35	--	nC
Reverse Recovery Time	T _{rr}		--	46	--	ns


Notes

1. Repetitive Rating: Pulse width limited by maximum junction temperature
2. EAS condition : $T_J = 25^{\circ}\text{C}$, $V_{DD} = -50V$, $V_{GS} = -10V$, $L = 0.5mH$, $R_g = 25\Omega$


The table shows the minimum avalanche energy, which is 64mJ when the device is tested until failure

3. Identical low side and high side switch with identical R_G


Gate Charge Test Circuit



Switch Time Test Circuit



EAS Test Circuit



Typical Characteristics $T_J = 25^\circ\text{C}$, unless otherwise noted

Figure 1. Output Characteristics




Figure 2. Transfer Characteristics




Figure 3. Drain Source On Resistance




Figure 4. Gate Charge




Figure 5. Capacitance





Figure 6. Source-Drain Diode Forward



Typical Characteristics $T_J = 25^\circ\text{C}$, unless otherwise noted

Figure 7. Drain-Source On-Resistance




Figure 8. Safe Operation Area




Figure 9. Maximum Continuous Drain Current vs Case Temperature






Figure 10. Normalized Maximum Transient Thermal Impedance



TO-252 Package Information



SYMBOL	mm		
	MIN	NOM	MAX
A	2.20	2.30	2.38
A1	0.00	-	0.12
A2	0.97	1.07	1.17
b	0.68	0.78	0.90
b3	5.20	5.33	5.46
c	0.43	0.53	0.61
D	5.98	6.10	6.22
D1	5.30REF		
E	6.40	6.60	6.73
E1	4.63	-	-
e	2.286BSC		
H	9.40	10.10	10.50
L	1.38	1.50	1.75
L1	2.90REF		
L2	0.51BSC		
L3	0.88	-	1.28
L4	0.50	-	1.00
L5	1.65	1.80	1.95
θ	0°	-	8°