

Product Data Sheet

DIN 41612 90° connector strip, Type C/2,
Part No. 103-90014






Illustration similar



Perpendicular



Through Hole



Rugged

- Connection length: 3 mm
- Number of poles: 32
- Soldering Techniques
- Grade 2



» to product on www.ept.de



» to product group DIN 41612

Product Data Sheet

DIN 41612 90° connector strip, Type C/2,
Part No. 103-90014



Technical Specifications

Basics

Specification	IEC 60603-2 (DIN 41612)
Performance Level	2
No. of Contacts	32
Termination Technology	Soldering Techniques
Termination Length	3 mm
Operating Temperature Range	-55°C to +125°C

Material

Insulator Material	Glass-fiber-reinforced PBT, UL 94 V-0
CTI value <i>IEC 60112</i>	200
Contact Material	copper alloy

Mechanical

Pitch	2.54 mm
Mating Force	30 N
Separating Force per Pin	> 0.15 N
Durability	400 insertion cycles

Electrical

Operational Current	2.6 A
Contact Resistance	20 mΩ
Clearance and Creepage	≥ 1.2 mm
Insulation Resistance	> 10 ⁶ MΩ
Test Voltage	1000 V

Processing

Soldering Temperature	up to 260°C
-----------------------	-------------

Approval / Compliance

UL file	E130314
Environment	RoHS compliant

Product Data Sheet

DIN 41612 90° connector strip, Type C/2,
Part No. 103-90014



Derating Diagram

Product Data Sheet



DIN 41612 90° connector strip, Type C/2,
Part No. 103-90014



Options

Board Lock 90°

Suitable for connectors with type B, C, D, E, F, G male connectors and R female connectors



Type of Insertion	Forces			PCB Thickness	Part Number
	F_m	not soldered F_h	soldered F_h		
Locked	< 30 N	> 10 N	> 20 N	≤ 1.6 mm	103-90014C1
Under Tension	< 30 N	> 7.5 N	> 20 N	> 1.6 mm	

Modifications

Available on request

- Leading and trailing contacts
- Special configuration
- Grade I + III or custom
- Custom length

Accessories

» DIN 41612 Kodierzange
Artikelnummer 894-301

Product Data Sheet

DIN 41612 90° connector strip, Type C/2,
Part No. 103-90014



Drawings

Component data in 2D and 3D format you can download here:

[» PDF](#)

[» 3D IGES](#)

[» 3D STEP](#)

[» 3D PDF](#)