

DESCRIPTION

GC8 is a premium grade specification lensed troffer series. This innovative, high quality luminaire is dedicated to the latest T8 lamp and micro electronic ballast technology for optimal performance and energy efficiency. The GC8 is compatible with all of today's popular ceiling systems and is available with a number of options and accessories for application versatility.

The GC8 Series features efficiency, quality and performance. The series is an excellent choice for commercial office spaces, schools, hospitals or retail merchandising areas.

SPECIFICATION FEATURES

Construction

Rigid housing is die formed of code gauge prime cold rolled steel and features full length dieformed stiffeners for added strength. Side flanges are hemmed. Innovative design provides superior lens brightness uniformity and visual comfort. Micro ballast cover*** reduces ballast shadow for superior lens brightness uniformity and is easily removed without tools. Die formed captive lampholder brackets fully enclose lampholder wiring permitting easy lampholder replacement. Heavy endplates are securely attached with interlocking tabs and screws. Four auxiliary fixture end suspension points provided. KOs for continuous row wiring. Endplates have integral Gridlock feature for safety and convenience.

Electrical

Ballasts are CBM/ETL Class "P" and are positively secured by mounting bolts. Pressure lock lampholders. UL/CUL listed. Suitable for damp locations.**

Finish

Multistage, iron phosphate pretreatment ensures maximum bonding and rust inhibition. Housing and ballast cover finished with new 90% reflective matte white enamel for superior performance. "PAF" Painted After Fabrication option also available.

Hinging/Latching


Positive cam action spring loaded steel latches with baked white enamel finish. Safety-lock Things allow hinging and latching either side.

Frame/Shielding


Die formed, heavy gauge, flat steel door with reinforced mitered corners and baked white enamel finish. Flat and regressed aluminum doors also available. Positive light seals. Light stabilized 100% virgin acrylic prismatic lens. Standard #12 pattern. Numerous additional shielding options available.

Controls


Fifth Light ballast options are offered for both 0-10V continuous dimming and DALI applications. Combine with energy-saving products like occupancy sensors, daylighting controls, and lighting relay panels from Cooper Controls (www.coopercontrol.com) to maximize energy savings.




MOUNTING DATA




DOOR FRAMES



LAMP CONFIGURATIONS



CEILING COMPATIBILITY



**GC8
232**

**1' X 4' TROFFER
2 LAMP**

Specification T8 Troffer



ENERGY DATA

Input Watts:
EB Ballast & STD Lamps
232 (61)
ES Ballast & STD Lamps
232 (71)


Luminaire Efficacy Rating
LER = FL-58
Catalog Number: GC8-232A
Yearly Cost of 1000 lumens,
3000 hrs at .08 KWH = \$4.15

*Standard G (Grid) Type Fixtures can be field converted by adding trim kits. See Compatibility Section or Consult Factory.
**Reference the lamp/ballast data in the Technical Section for specific lamp/ballast requirements.
***Full sized ballast cover for emergency option.

LAMPS CONTAIN MERCURY. DISPOSE ACCORDING TO LOCAL, STATE OR FEDERAL LAWS



PHOTOMETRICS

**GC8-232A**

Electronic Ballast

(2) FO32/35K lamps
2800 lumensSpacing criterion:
(II) 1.2 x mounting
height, (⊥) 1.2 x
mounting height

Efficiency 71.6%

Test Report:
GC8232A.IES

LER = FL-58

Yearly Cost of 1000
lumens, 3000 hrs at
.08 KWH = \$4.15**Coefficients of Utilization**

Effective floor cavity reflectance										20%											
rc	80%				70%				50%				30%				10%				0%
rw	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																					
0	85	85	85	85	83	83	83	83	80	80	80	76	76	76	73	73	73	72			
1	79	76	74	71	77	75	72	70	72	70	68	69	67	66	66	65	64	62			
2	73	68	64	61	71	67	63	60	64	61	58	62	59	57	60	58	56	54			
3	68	61	56	52	66	60	56	52	58	54	51	56	53	50	55	52	49	48			
4	63	55	50	45	61	54	49	45	53	48	45	51	47	44	49	46	43	42			
5	58	50	44	39	56	49	43	39	47	43	39	46	42	38	45	41	38	37			
6	54	45	39	35	52	44	39	35	43	38	34	42	37	34	41	37	34	32			
7	50	41	35	31	48	40	35	31	39	34	30	38	34	30	37	33	30	29			
8	46	37	31	27	45	36	31	27	35	30	27	34	30	27	34	29	26	25			
9	42	33	27	24	41	33	27	23	32	27	23	31	27	23	30	26	23	22			
10	39	30	25	21	38	30	24	21	29	24	21	28	24	21	28	24	21	19			

Zonal Lumen Summary

Zone	Lumens	%Lamp	%Fixture
0-30	1380	24.6	34.4
0-40	2196	39.2	54.8
0-60	3452	61.6	86.1
0-90	4011	71.6	100.0
0-180	4011	71.6	100.0

Typical VCP Percentages

Room Size (Ft.)	Height Along		Height Across	
	8.5'	10.0'	8.5'	10.0'
20 x 20	60	64	60	65
30 x 30	52	57	51	56
30 x 60	43	46	40	44
60 x 30	54	59	54	58
60 x 60	44	47	41	45

Candlepower

Angle	Along II	45°	Across ⊥
0	1782	1782	1782
5	1768	1778	1779
10	1745	1759	1763
15	1707	1724	1728
20	1651	1668	1662
25	1574	1582	1559
30	1471	1463	1419
35	1343	1312	1258
40	1186	1133	1100
45	1002	943	931
50	813	760	749
55	633	579	549
60	475	401	401
65	348	261	305
70	253	175	245
75	193	140	212
80	140	117	156
85	75	65	84
90	0	0	0

ORDERING INFORMATION

SAMPLE NUMBER: GC8-232A-120V-EB81-U

Width
Blank=1' Width

Trim Type
G=Grid/Lay-in (Standard)⁽¹⁾
G=Concealed T
G=Slot Grid
F=Flange Trim
C=Modular Trim

Series
C8=Specification T8 Troffer

Door Frame
Standard=Flat White Steel Door
(Leave Blank)
FA=Flush White Extruded
Aluminum c/w Spring Latch
RA=Regressed White Extruded
Aluminum
FAN=Flush Natural Anodized
Extruded Aluminum
RAN=Regressed Natural
Anodized Extruded Aluminum
FAB=Flush Black Extruded
Aluminum
RAB=Regressed Black Extruded
Aluminum

Number of Lamps
2=2 Lamps
(Not included)

Wattage
32=32W T8 (48")

Shielding
A=#12 Acrylic Pattern
A125=#12 Pattern Acrylic (.125" Thickness)
A19/156=#19 Pattern Acrylic (.156" Thickness)
DA=Dropped Dish Matte White Acrylic
IMA48=Injection Molded Acrylic (.150" Thick)

Voltage⁽²⁾
120V=120 Volt
277V=277 Volt
347V=347 Volt
UNV=Universal Voltage 120-277⁽³⁾

Options
GL=Single Element Fuse
GM=Double Element Fuse
Lamps=Lamps Installed
Flex=Flex Installed
EL=Emergency Installed

Ballast Type

EB8_=T8 Electronic Start.
Total Harmonic
Distortion < 10%
EB8_/PLUS= T8 Electronic Start.
Total Harmonic
Distortion < 10%. High
Ballast Factor > 1.15.

ER8_= T8 Electronic Program
Rapid Start. Total Harmonic
Distortion < 10%

High Performance T8 Ballasts

HB8_=T8 Electronic Instant Start.
Total Harmonic Distortion <
10%. Standard Ballast
Factor .86 – .88

HB8_L=T8 Electronic Instant Start.
Total Harmonic Distortion <
10%. Low Ballast Factor
.77 – .82

HB8_N=T8 Electronic Instant Start.
Total Harmonic Distortion <
10%. Normal Ballast Factor
1.0

HB8_H=T8 Electronic Instant Start.
Total Harmonic Distortion <
10%. High Ballast Factor
1.15 – 1.20

HR8_T8 Electronic Program Rapid
Start. Total Harmonic
Distortion < 10%. Standard
Ballast Factor .86 – .88

HR8_DIM=T8 Electronic Program
Rapid Start. Total
Harmonic Distortion <
10%. Step Dimming.
Ballast Factor .88

HR8_L=T8 Electronic Program
Rapid Start. Total Harmonic
Distortion < 10%. Low
Ballast Factor .71 – .79

HR8_H=T8 Electronic Program
Rapid Start. Total Harmonic
Distortion < 10%. High
Ballast Factor 1.15 – 1.20

0-10V Dimming Ballasts⁽⁵⁾

5LTV8_=T8 0-10V Program Rapid
Start. Total Harmonic
Distortion < 10%.
Ballast Factor 0.87

5LTVS8_=T8 0-10V Spec Grade
Program Rapid Start.
Total Harmonic Distortion
< 10%. Ballast Factor 0.87⁽⁶⁾

Fifth Light DALI Ballasts⁽⁴⁾

5LT8_=T8 DALI Program Rapid Start.
Total Harmonic Distortion <
10%. Ballast Factor 1.0

Options

RLS=Rotor Lock Socket
(T8 Lamp only)
FR=Fire Rated Label
MEP=Modified End Plate
REP=Riveted End Plate
PAF=Painted After
Fabrication

Packaging

U=Unit Pack
PAL=Job Pack, out of carton
PALC=Job Pack, in carton

ACCESSORIES

EO-CLIP-U=T-BAR Safety
Earthquake Clips⁽¹⁾

NOTES : ⁽¹⁾ An EQ Grid Clip is recommended for all 9/16" ceiling systems. Four required per fixture. ⁽²⁾ Products also available in non-US voltages and frequencies for international markets. ⁽³⁾ Not available when specifying emergencies, voltage must be specific. ⁽⁴⁾ For a complete listing of Fifthlight Technology products and other solutions from Cooper Controls, visit www.coopercontrol.com. ⁽⁵⁾ 0-10V ballast do not include DALI feature. Please select DALI ballast for use with Fifth Light system. ⁽⁶⁾ Specification grade 0-10V dimming ballast are NEMA premium and CEE listed. They are compatible with low mercury and energy saving lamps.

Specifications & dimensions subject to change without notice. Consult your Cooper Lighting Representative for availability and ordering information.

Number of Ballasts

1=1 Ballast
2=2 Ballasts
3=3 Ballasts

SHIPPING DATA

Catalog No.	Wt.
GC8-232A	19 lbs