

SLF7045T-150M1R5-H



Applications	Automotive Grade
Feature	AEC-Q200
	Wire Wound
	Magnetic Shield
	Ferrite Core
Series Type	SLF-H
Status	EOL announced
	Recommended Alternate Part No. : VLS5045EX-150M-H (Interchangeability is not guaranteed.)
	Discontinue Issue Date : May.14, 2024
	Last Purchase Order Date : Mar.31, 2026
	Last Shipment Date : Dec.31, 2026
Brand	TDK



Size	
Length(L)	7.00mm ±0.20mm
Width(W)	7.00mm ±0.20mm
Thickness Height	4.50mm ±0.30mm
Recommended Land Pattern (A)	1.50mm Nom.
Recommended Land Pattern (B)	4.80mm Nom.
Recommended Land Pattern (C)	2.20mm Nom.

Electrical Characteristics	
Inductance	15μH ±20% at 100kHz
Rated Current (L Change) [Typ.]	
Rated Current (L Change) [Max.]	1.5A (10% Down)
Rated Current (Temperature Rise) [Typ.]	1.46A (20°C Rise)
Rated Current (Temperature Rise) [Max.]	
DC Resistance [Typ.]	68mΩ
DC Resistance [Max.]	81.6mΩ
Rated Voltage [Max.]	
Self Resonant Frequency [Min.]	
Self Resonant Frequency [Typ.]	
Q [Min.]	
Q [Typ.]	

Other	
Operating Temp. Range (Including Self-Temp. Rise)	-40 to 125°C

! Images are for reference only and show exemplary products.
! This PDF document was created based on the data listed on the TDK Corporation website.
! All specifications are subject to change without notice.

SLF7045T-150M1R5-H









Soldering Method	Reflow Iron Soldering
AEC-Q200	YES
Packing	Embossed (Plastic)Taping [330mm Reel, Tape width 16mm]
Package Quantity	1000pcs
Weight	0.58g

SLF7045T-150M1R5-H




Characteristic Graphs(This is reference data, and does not guarantee the products characteristics.)



SLF7045T-150M1R5-H



Characteristic Graphs(This is reference data, and does not guarantee the products characteristics.)



SLF7045T-150M1R5-H



Associated Images

