


Technical specification :


Rated voltage: IEC 61076-2-104	30 V
Current rating: IEC 61076-2-104	3 A at 40°C
Insulation resistance: IEC 60512	$\geq 100 \text{ M}\Omega$
Pollution degree: IEC 60664-1	3/2
Degree of protection: IEC 60529	IP 67, in mated condition
Temperature range: IEC 60664-1	-30°C ... +80°C
Mating cycles: IEC 60512-9a	≥ 100

Materials:

Contact:	CuZn
Contact plating:	Nickel, gold plated
Contact carrier:	TPU GF, UL 94
Moulding body:	TPU, UL 94, grey

Contact assignment:

1) brown	■
2) white	■
3) blue	■
4) black	■



Part no:	Description:	Length L:	Cable:
42-10819	SAL - 8 - RKS4 - RSS4 - 0,3 / A1	0,3m	PVC, grey, 4x0,25mm ² Cable: 781-A12400
42-10820	SAL - 8 - RKS4 - RSS4 - 0,6 / A1	0,6m	
42-10821	SAL - 8 - RKS4 - RSS4 - 1,5 / A1	1,5m	
42-10822	SAL - 8 - RKS4 - RSS4 - 3 / A1	3,0m	
42-xxxxx	SAL - 8 - RKS4 - RSS4 - ... / A1	x	

D see data sheet cable

DO NOT ALTER CAD DRAWING BY HAND Directive 2002/95/EC RoHS compliant	Index: a 21.03.11 VF Ä3941 data sheet revised	dim. in mm	title: Connecting cable Ø8, female connector axial - male connector axial	
	tolerance of cable: $L \leq 4\text{m}: L + 40\text{mm}$ $L > 4\text{m}: L + 1\%$		dwg no: 42K1A170	
	THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH		part no: see table	