






THESE DRAWINGS ARE THE PROPERTY OF QUALTEK ELECTRONICS AND NOT TO BE REPRODUCED FOR OR COMMUNICATED TO A THIRD PARTY WITHOUT THE EXPRESS WRITTEN PERMISSION OF AN OFFICER OF QUALTEK ELECTRONICS.

REVISION			
REV.	DESCRIPTION	DATE	APPROVED
B	RoHS Compliancy	06-01-06	DP
C	Updated Approvals	04-27-09	LY
D	Added UL File Number to Notes	01-12-10	LY
E	Updated Approvals and Dim	07-21-26	LY



PANEL CUTOUT



NOTES:

STANDARD: IEC 60320-1
RATING:
UL, cUL: 20A 125/250V AC
TUV, CCC: 16A 250V AC
APPROVALS: UL, cUL, TUV, CCC
UL FILE: E139605
IEC 60320 C19
RoHS COMPLIANT

CONTROLLED

Dim range (mm)	Tolerance +/- (mm)	Qualtek Electronics Corp. PPC DIVISION		
		Part Number: 743W-00/03	RoHS Compliant	
0-1	0.15	Description: AC RECEPTACLE		
1-6	0.20			
6-18	0.30		UNIT: mm	REV. E
18-50	0.50			
50-120	0.70			
120-250	0.90			
250-500	1.20	B.Zhang 10-27-03	10-27-03	JJH / 10-27-03