


 [Live Product Chat](#)



✓ Active

 Add to Part List

 [Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

- Daughtercard
- RT2 Series
- VITA 41/VITA 46 Configuration
- Spacing Between Cards = 20.30 mm
- Module Type = Center

[View all Features](#) | [Find Similar Products](#)

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [View Mating Products \(2\)](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)
- ▶ [Request Samples](#)

Documentation & Additional Information

- [RIGHT-ANGLE PLUG ASSEMBLY CENTER, 20.3mm, MultiGig R...](#)
(PDF, English)

- None Available

- [MultiGig Signal Connector, Tiers 1 and 2 \(PDF, English\)](#)

- [MULTIGIG RT Signal Connectors](#) (PDF, English)

- None Available

- None Available

- Product Line Information

- Tooling
- Mating Products (2)

List all Documents

Product Features (Please use the Product Drawing for all design activity)

- Product Type = Daughtercard
- Mount Angle = Right Angle
- Termination Type = Differential

- Module Type = Center

- REF = P20
- Board = Switch-High
- Part Designation = T2-C08-R
- Data Rate (Gb/s) = 6.500

- Solder Tail Contact Plating = Tin over Nickel

- Series = RT2
- Number of Columns = 16
- Flammability Rating = UL 94V-0
- Post Material = Brass
- Post Plating = Nickel

- Spacing Between Cards (mm [in]) = 20.30
[0.800]
- Contact Material = Phosphor Bronze
- Contact Mating Area Plating Material = Tin over Nickel

- Housing Material = Liquid Crystal Polymer (LCP)
- Housing Color = Black

- Density = 85 lines/inch

- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Not relevant for lead free process
- VITA 41/VITA 46 Configuration = Yes
- RoHS/ELV Compliance History = Always was RoHS compliant

- Brand = Tyco Electronics