




Part Number : [1053252002](#)
Product Description : Nano-Fit Terminal
Position Assurance (TPA) Retainer, 2.50mm
Pitch, 2 Circuits, Natural
Series Number : 105325
Status : Active
Product Category : Connector Accessories



Documents & Resources

Drawings
[1053252002_sd.pdf](#)
[PK-105325-100-000.pdf](#)

3D Models and Design Files
[1053252002_stp.zip](#)

Specifications
[AS-105300-100-001.pdf](#)
[PS-105300-100-001.pdf](#)
[1053000000-TS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Connector Accessories
Series	105325
Description	Nano-Fit Terminal Position Assurance (TPA) Retainer, 2.50mm Pitch, 2 Circuits, Natural
Comments	Operating temperature is -40° to +105° for tin and -40° to +115° for gold
Component Type	Terminal Position Assurance
Product Name	Nano-Fit
UPC	889056029124

Physical

Circuits (Loaded)	2
Circuits (maximum)	2
Color - Resin	Natural
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	0.080/g
Number of Rows	1
Packaging Type	Bag
Temperature Range - Operating	-40° to +125°C

Use with Part(s)

Description	Part Number
Nano-Fit TPA Capable Single Row Receptacle Housings	<u>105307</u>

Nano-Fit TPA Capable Dual Row Receptacle Housings	<u>105308</u>
Nano-Fit TPA Capable Single Row Plug Housings	<u>200277</u>
Nano-Fit Dual Row TPA Capable Plug Housings	<u>201444</u>
Nano-Fit BMI TPA Capable Plug Housings	<u>224556</u>

This document was generated on Mar 18, 2025