




TFE-24-X-STK Product Details

[Share](#) [Print](#) [Email](#)

TFE-24-X-STK

TE Internal Number: 5950042002



Heat Shrink Tubing

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Heat Shrinkable Tubing
- Product Name = TFE
- Product Source = U.K.
- Flexible
- Thin Wall Style

[View all Features](#)

Quick Links

- [Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

[Add to My Part List](#)
[Request Sample](#)
[Find Similar Products](#)
[Buy Product](#)

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Heat Shrinkable Tubing
- Color = Clear

Dimensions:

- Expanded ID, Min. (mm [in]) = 1.20 [0.047]
- Recovered ID, Max. (mm [in]) = 0.68 [0.027]
- Cut Length (mm [in]) = 1220.00 [48.031]

Body Features:

- Product Name = TFE
- Pliancy = Flexible
- Wall Style = Thin
- Wall Type = Single
- Material = Polytetrafluoroethylene (PTFE)
- Shrink Ratio = 1.8:1
- Fluid Type = Brake Fluid, Chemicals/Solvents, Water
- Resistant To = Fluids, Mechanical Damage
- Wall Thickness - Full Recovery (Nominal) (mm [in]) = 0.25 [0.010]

Housing Features:

- Material Systems = No

Industry Standards:

- Government/Industry Qualification = No
- Flammability Rating Type = Flame-Retardant
- UL Rating = None
- CSA Certified = No
- Approved Standards = BS 4G-198 Part 4 Type 21A, DEF Std 59-97 Type 5B, SAE AMS-DTL-23053/12
- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Environmental:

- Fluid Resistance = Splash Protection
- Operating Temperature (°C) = -67 - +250

Conditions for Usage:

- Full Recovery Temperature (°C) = 340
- Shrink Temperature, Min. (°C) = 340
- High Temperature Compatible = Yes

Operation/Application:

- Application = Insulation and Protection
- Emission Free = No
- Product Use = Couplings, Hydraulic Hose

Packaging Features:

- Packaging Method = Stick

Product Availability:

- Product Source = U.K.

Other:

- Brand = Raychem

Corporate Information

[About TE](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)
[Terms & Conditions](#)
[Privacy Policy](#)

Quick Links

[Distributor Inventory](#)
[Product Cross Reference](#)
[Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Knowledge Base](#)
[Manage Your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

 Enter your email address
