



Part Number : [02082004](#)  
Product Description : MLX Crimp Terminal  
42023, 20-14 AWG, Bag Tin (Sn)  
Series Number : 42023  
Status : Active  
Product Category : Crimp Terminals  
Engineering Number : 42023-2A1L  
Packaging Alternative : 02082003 (Reel)




## Documents & Resources

Drawings  
[002082004\\_sd.pdf](#)

Specifications  
[PS-42022-0001-001.pdf](#)  
[TS-42022-0001-001.pdf](#)

## Product Environment Compliance

### Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## EU RoHS Certificate of Compliance

---

### Part Details

#### General

Status	Active
Category	Crimp Terminals
Series	42023
Description	MLX Crimp Terminal 42023, 20-14 AWG, Bag Tin (Sn)
Application	Power, Wire-to-Wire
Product Name	MLX
UPC	800753618725

#### Physical

Gender	Male
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.332/g
Packaging Type	Bag
Plating min - Mating	0.508µm
Plating min - Termination	0.508µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.52-3.30mm
Wire Size (AWG)	14, 16, 18, 20
Wire Size mm <sup>2</sup>	N/A

#### Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

---

### Application Tooling

## Global

Description	Part Number
Extraction Tool for MLX 2.13mm Diameter Pin and Socket Crimp Terminals	<u>11010168</u>
PremiumGrade Hand Crimp Tool for MLX Pin and Socket Terminals, 20-14 AWG	<u>638116800</u>

---

This document was generated on Mar 16, 2025