



REVISIONS					
REV	ECO	DESCRIPTION	DATE	BY	APPR
A1	-	RELEASED DRAWING	Sep-25-2020	Ronald	Tommy










NOTES:
1. MATERIAL:
   1.1 HOUSING BODY: ZINC DIE- CAST, NICKEL PLATED
   1.2 INSULATION INSERT: PA66 ,UL94 V0
   1.3 SEAL: SILICONE RUBBER
2. SPECIFICATIONS:
   2.1 CURRENT RATING: 86 AMPS MAX.
   2.2 VOLTAGE RATING: 630 V A C/DC
   2.3 OPERATING TEMPERATURE: -40°C TO +125°C
   2.4 DIELECTRIC WITHSTANDING VOLTAGE:
   LESS THAN 2 MILLIAMP S CURRENT IEAKAGE @ 5000 VOLTS A C
   2.5 DEGREE OF PROTECTION: I P67 (MATED CONDITION)
   2.6 DEGREE OF POLLUTION: 3 PER UL840
   2.7 OVERVOLTAGE CATEGORY: I II PER UL840
   2.8 MATING CYCLE DURABILITY : >100 CYCLES
   2.9 RoHS COMPLIANT
3. ALL DIMENSIONS ARE FOR REFER ENCE USE ONLY.
4. "*" DENOTE KEY POSTION OF "N ","W","X","Y" OR "Z".



PANEL CUT OUT REFERENCE

KEY POS	PART NUMBER	A	B	C	D
N	RTHP0203SNH	105˚	140˚	215˚	265˚
W	RTHP0203SWH	79˚	140˚	215˚	265˚
X	RTHP0203SXH	105˚	126˚	215˚	265˚
Y	RTHP0203SYH	105˚	140˚	215°	259°
Z	RTHP0203SZH	105˚	140˚	215˚	330˚

QUANTITY	PART NUMBER	DESCRIPTION	ITEM

MATERIALS LIST

UNLESS OTHERWISE SPECIFIED
1) All dimensions are in metric(mm).
2) Tolerances are as follows:
1 PL DEC ±0.30 | Fractions ±1/64
2 PL DEC ±0.15 | Angles ±1°
3 PL DEC ±0.05
3) Note reference = X

MATERIAL SPECIFICATIONS:

PROCESS SPECIFICATIONS:

NEXT ASS'Y:

SIGNATURES		DATE
DRAWN:	Ronald	Sep-25-2020
CHECKED:	Flan	Sep-27-2020
ENGINEER:		
APPROVAL:	Tommy	Sep-28-2020
CUSTOMER:		

THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY. DESIGN FEATURE S, SPECIFICATIONS AND PERFORMANCE D ATA SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIG HTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL MANUFACTURING VARIATIONS.

Amphenol
Sine Systems - www.amphenol-sine .com
44724 Morley Drive
Clinton Township, MI 48036

3 Position Square Flange Receptacle, Female, Size 8 (3.6mm), Shell Size #20, High Amperage 630V

SIZE	TYPE	DWG NO:	REVISION
B	C-	RTHP0203S*H	A1

SCALE: NONE SHEET 1 OF 1

TITLE: ECONOMATE MINI HIGH AMP, RECEPTACLE,3 POS,SIZE 20
DWG NO: RTHP0203S*H
REV: A1
SH: 1
OF: 1

Downloaded from Arrow.com.