



+ CONNECTORS

CONNECTOR HOUSINGS



✓ Active

TE CONNECTIVITY (TE)
10POS,NANOMQS,REC HSG,COD B

2302475-2
TE Internal Number: 2302475-2

- EU RoHS Compliant
- EU ELV Compliant
- Connector System Wire-to-Board, Wire-to-Device, Wire-to-Wire
- Connector Style Housing for female terminals
- Mating Tab Width (mm) .5
- Sealable No
- Circuit Application Signal

↓ PRODUCT DRAWING
English

↓ 3D PDF

DOCUMENTATION

Product Drawings

6-20 Pol., NanoMQS, Buchsengehaeuse 6-20 POS., NanoMQS, REC. HOUSING
PDF
English

CAD Files

3D PDF
PDF
3D

Customer View Model
2D_DXF.ZIP
English

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Connector System Wire-to-Board, Wire-to-Device, Wire-to-Wire

Connector Style Housing for female terminals

Sealable No

Hybrid Connector No

Terminates To Wire & Cable

Primary Locking Feature On the terminal

Row-to-Row Spacing (mm) 1.5

Configuration Features

Number of Positions 10

Number of Rows 2

Electrical Characteristics

Nominal Voltage Architecture (V) 12

Body Features

Connector Code B

Body Material PBT GF

Color Natural

Contact Features

Mating Tab Width (mm) .5

Mechanical Attachment

Mounting Feature No

Terminal Position Assurance Yes

Polarized Yes

Housing Features

Pitch (mm) 1.8

Usage Conditions

Operating Temperature Range (°C) -40 – 130
Operating Temperature (Max) (°C) 130

Operation/Application

Circuit Application Signal

Industry Standards

UL Flammability Rating UL 94-HB

Other

Connector Position Assurance Capable No

Statement of Compliance

Statement of Compliance

PDF