


NPCAP™-PSC Series

- Super low ESR, high ripple current capability
- Rated voltage range : 2.5 to 16V_{dc}
- Nominal capacitance range : 270 to 2,700μF
- Endurance : 15,000 hours at 105°C
- Suitable for DC-DC converters, voltage regulators and decoupling applications for computer motherboards
- Added 2.5V 820μF (ESR 5mΩ max.)
- Solvent resistant type (see PRECAUTIONS AND GUIDELINES)
- RoHS2 Compliant
- Halogen Free





SPECIFICATIONS

Items	Characteristics						
Category							
Temperature Range	-55 to +105℃						
Rated Voltage Range	2.5 to 16V _{dc}						
Capacitance Tolerance	± 20% (M) (at 20℃, 120Hz)						
Leakage Current	I=0.2CV or 500μA, whichever is greater. Where, I : Max. leakage current (μA), C : Nominal capacitance (μF), V : Rated voltage (V _{dc}) (at 20℃ after 2 minutes)						
*Note							
Dissipation Factor (tan δ)	0.10 max. (at 20℃, 120Hz)						
Low Temperature Characteristics (Max.Impedance Ratio)	Z(-25℃)/Z(+20℃)≤1.15 Z(-55℃)/Z(+20℃)≤1.25 (at 100kHz)						
Endurance	The following specifications shall be satisfied when the capacitors are restored to 20℃ after the rated voltage is applied for 15,000 hours at 105℃.						
	Appearance		No significant damage				
	Capacitance change		≤ ±20% of the initial value				
	D.F. (tan δ)		≤150% of the initial specified value				
	ESR		≤150% of the initial specified value				
	Leakage current		≤The initial specified value				
Bias Humidity Test	The following specifications shall be satisfied when the capacitors are restored to 20℃ after subjecting them to DC voltage at 60℃, 90 to 95% RH for 1,000 hours.						
	Appearance		No significant damage				
	Capacitance change		≤ ±20% of the initial value				
	D.F. (tan δ)		≤150% of the initial specified value				
	ESR		≤150% of the initial specified value				
	Leakage current		≤The initial specified value				
Surge Voltage Test	The capacitors shall be subjected to 1,000 cycles each consisting of charge with the surge voltage specified at 105℃ for 30 seconds through a protective resistor(R=1kΩ) and discharge for 5 minutes 30 seconds.						
	Rated voltage (V _{dc})		2.5	4.0	6.3	10	16
	Surge voltage (V _{dc})		2.9	4.6	7.2	12	18
	Appearance		No significant damage				
	Capacitance change		≤ ±20% of the initial value				
	D.F. (tan δ)		≤150% of the initial specified value				
	ESR		≤150% of the initial specified value				
	Leakage current		≤The initial specified value				
	Failure Rate	0.5% per 1,000 hours maximum (Confidence level 60% at 105℃)					

*Note : If any doubt arises, measure the leakage current after the following voltage treatment.
Voltage treatment : DC rated voltage is applied to the capacitors for 120 minutes at 105°C.

DIMENSIONS [mm]

- Terminal Code : E




Size code	H08	HB5	JB5	JC5
φD	8.0	8.0	10.0	10.0
φd	0.6	0.8(Note1)	0.8(Note1)	0.6
F	3.5	3.5	5.0	5.0
φD'	φD+0.5max.			
L'	L+1.0max.		L+1.5max.	

Note1 : 0.6 for rated volt 16V.


MARKING

EX) 2.5V820μF



NPCAP™-PSC Series

◆PART NUMBERING SYSTEM



Please refer to "Product code guide (conductive polymer type)"

(Note2) PSC series, 2.5V820μF(ESR 5mΩ max.) has supplement code "J".
Can case, terminal and terminal plating are the same as all others in PSC series.

◆STANDARD RATINGS

WV (V _{dc})	Cap (μF)	Case size φ D × L (mm)	ESR (mΩ max./20°C, 100k to 300kHz)	Rated ripple current (mA _{rms} /105°C, 100kHz)	Part No.
2.5	560	8 × 8	7	6,100	APSC2R5E□□561MH08S
	820	8 × 8	5	6,100	APSC2R5E□□821MH08J
	820	8 × 8	7	6,100	APSC2R5E□□821MH08S
	1,000	8 × 8	7	6,100	APSC2R5E□□102MH08S
	1,000	8 × 11.5	7	6,100	APSC2R5E□□102MHB5S
	1,500	8 × 11.5	7	6,100	APSC2R5E□□152MHB5S
	2,700	10 × 11.5	8	5,560	APSC2R5E□□272MJB5S
4	560	8 × 8	7	6,100	APSC4R0E□□561MH08S
	680	8 × 11.5	7	6,100	APSC4R0E□□681MHB5S
	1,000	10 × 11.5	6	6,640	APSC4R0E□□102MJB5S
6.3	470	8 × 8	8	5,700	APSC6R3E□□471MH08S
	560	8 × 8	8	5,700	APSC6R3E□□561MH08S
	820	10 × 11.5	7	6,640	APSC6R3E□□821MJB5S
	1,500	10 × 11.5	10	5,560	APSC6R3E□□152MJB5S
10	390	8 × 11.5	9	5,650	APSC100E□□391MHB5S
	680	10 × 11.5	7	6,100	APSC100E□□681MJB5S
16	270	8 × 11.5	11	5,080	APSC160E□□271MHB5S
	330	10 × 11.5	10	6,100	APSC160E□□331MJB5S
	330	10 × 12.5	10	6,100	APSC160E□□331MJC5S
	470	10 × 11.5	10	6,100	APSC160E□□471MJB5S

□□ : Enter the appropriate lead forming or taping code.

◆RATED RIPPLE CURRENT MULTIPLIERS

● Frequency Multipliers

Frequency(Hz)	120	1k	10k	50k	100k to 500k
Radial lead type	0.10	0.35	0.60	0.80	1.00