Part Number : 26202141
Product Description : KK 396 Wire-to-Board Header, Vertical Round Pin, 14 Circuits, Tin (Sn) Plating, with Mating Pin Length of 11.43mm (.450")
Series Number : 3192
Status : Active
Product Category : PCB Headers and Receptacles
Engineering Part Number : 319214A



Documents and Resources

Drawings

026202141_sd.pdf

PK-3192-001-001.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Symbol and Footprint (Multi-Format)

SYM-26-20-2141-001.zip

Specifications

PS-99020-0087-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 33
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC

Downloaded from Arrow.com.

- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	3192
Description	KK 396 Wire-to-Board Header, Vertical Round Pin, 14 Circuits, Tin (Sn) Plating, with Mating Pin Length of 11.43mm (.450")
Application	Board-to-Board, Wire-to-Board
Component Type	PCB Header
Product Name	KK 396
UPC	800753734562

Agency

UL	E29179

Electrical

Current - Maximum per Contact	7.0A
Voltage - Maximum	250V

Physical

Breakaway	No
Circuits (Loaded)	14
Circuits (maximum)	14

Downloaded from Arrow.com.

Color - Resin	Natural
Durability (mating cycles max)	25
First Mate / Last Break	No
Flammability	94V-2
Gender	Male
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	No
Lock to Mating Part	No
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Mounting Style	Through Hole
Net Weight	3.399/g
Number of Rows	1
Orientation	Vertical
Packaging Type	Bag
PCB Locator	No
PCB Retention	No
PCB Thickness - Recommended	1.60mm
PC Tail Length	4.45mm
Pitch - Mating Interface	3.96mm
Pitch - Termination Interface	3.96mm
Plating min - Mating	5.080µm
Plating min - Termination	5.080µm
Polarized to Mating Part	No
Polarized to PCB	No
Shrouded	Unshrouded
Stackable	Yes
Temperature Range - Operating	See Product Specification
Termination Interface Style	Through Hole

Solder Process Data

Max-Duration	5

Downloaded from Arrow.com.

Lead-Free Process Capability	WAVE
Max-Cycle	1
Max-Temp	235

Mates With / Use With

Mates with Part(s)

Description	Part Number
KK 3.96mm Single Row Crimp Housings	3069

Downloaded from Arrow.com.