



Datasheet of SAW Device


SAW Single Filter

for Band29 (FLO) / Unbalanced / 5pin /1109

Murata PN: SAFFB722MAA0F0A

■ Feature

- Low Insertion Loss
- Small Size 1.1 x 0.9 mm
- World First Release



Note : Murata SAW Component is applicable for Cellular /Cordless phone (Terminal) relevant market only.

Please also read caution at the end of this document.

SAFFB722MAA0F0A (Band29 (FLO) / Unbalanced / 5pin / 1109)

Revision No.	Date	Description
SAFFB722MAA0F0A_rev. A	Dec-12-2012	■ Initial Release
SAFFB722MAA0F0A_rev. B	Feb-13-2013	■ Updated for ES2.0
SAFFB722MAA0F0A_rev. C	May-24-2013	■ Updated Final Version
SAFFB722MAA0F0A_rev. D	Oct-25-2013	■ revisethe Spec of VSWR

- Operating temperature : -30 to +85 deg.C
- Storage temperature : -40 to +85 deg.C
- Input Power : +15 dBm 2000 h
- D.C. Volatage between the terminals : 3V (25+/-2 deg.C)
- Minimum Resistance between the terminals : 10M ohm
- RoHS compliance : Yes

SAFFB722MAA0F0A (Band29 (FLO) / Unbalanced / 5pin / 1109)

Electrical Characteristic < Single Filter >

Matching Impedance (nominal)

- : Unbalance Port : 50 ohm
- : Unbalance Port-Lch : 50 ohm


Item	Characteristics (-30 to +85 deg.C)			Unit	Note
	min.	typ.	max.		
Center Frequency		722.5		MHz	
Insertion Loss	717. to 728. MHz	1.7	2.5	dB	
	717. to 728. MHz		2.0	dB	+23 to +27deg.C
	717.25 to 727.75 MHz	1.7	2.5	dB	
	717.25 to 727.75 MHz		2.0	dB	+23 to +27deg.C
Ripple Deviation	717. to 728. MHz	0.3	1.0	dB	Any 5MHz
	717. to 728. MHz		0.5	dB	+23 to +27deg.C, Any 5MHz
	717.25 to 727.75 MHz	0.3	1.0	dB	Any 5MHz
	717.25 to 727.75 MHz		0.5	dB	+23 to +27deg.C, Any 5MHz
VSWR	717. to 728. MHz	1.5	2.0		
	717.25 to 727.75 MHz	1.5	2.0		
Absolute Attenuation	10. to 698. MHz	40	50	dB	
	739. to 746. MHz	10	20	dB	
	746. to 6000. MHz	26	31	dB	
	1710. to 1755. MHz	35	41	dB	B4 TX for CA
	1850. to 1910. MHz	33	39	dB	B2 TX for CA
	2151.75 to 2183.25 MHz	28	36	dB	3f
	2400. to 2500. MHz	30	36	dB	ISM2.4
	4900. to 5950. MHz	26	31	dB	ISM 5G
	6000. to 12750. MHz	12	20	dB	
	698. to 704. MHz	30	41	dB	Average over ch52
	704. to 710. MHz	4	10	dB	Average over ch53
	734. to 739. MHz	2	5	dB	Average

* Typical value at 25±2deg.C


SAFFB722MAA0F0A (Band29 (FLO) / Unbalanced / 5pin / 1109)

Electrical Characteristic < Single Filter >

Narrow-Segment




Wide-Segment




SAFFB722MAA0F0A (Band29 (FLO) / Unbalanced / 5pin / 1109)

Dimensions of Tape & Reel unit: mm


Carrier Tape



Tape



Reel



SAFFB722MAA0F0A (Band29 (FLO) / Unbalanced / 5pin / 1109)

Marking Code

Table A: Month Code

2009	Jan.	Feb.	Mar.	Apr.	May	Jun.	Jul.	Aug.	Sep.	Oct.	Nov.	Dec.
2013	A	B	C	D	E	F	G	H	J	K	L	M
2017												
2010	Jan.	Feb.	Mar.	Apr.	May	Jun.	Jul.	Aug.	Sep.	Oct.	Nov.	Dec.
2014	N	P	Q	R	S	T	U	V	W	X	Y	Z
2018												
2011	Jan.	Feb.	Mar.	Apr.	May	Jun.	Jul.	Aug.	Sep.	Oct.	Nov.	Dec.
2015	a	b	c̄	d	e	f	g	h	j	k	l	m
2019												
2012	Jan.	Feb.	Mar.	Apr.	May	Jun.	Jul.	Aug.	Sep.	Oct.	Nov.	Dec.
2016	n	p	q	r	s	t	u	v	w	x	y	z
2020												

Table B: Date Code

date	1st	2nd	3rd	4th	5th	6th	7th	8th	9th	10th	
code	A	B	C	D	E	F	G	H	J	K	
date	11th	12th	13th	14th	15th	16th	17th	18th	19th	20th	
code	L	M	N	P	Q	R	S	T	U	V	
date	21st	22nd	23rd	24th	25th	26th	27th	28th	29th	30th	31st
code	W	X	Y	Z	a	b	c̄	d	e	f	g

Important Notice (1/2)

PLEASE READ THIS NOTICE BEFORE USING OUR PRODUCTS.

Please make sure that your product has been evaluated and confirmed from the aspect of the fitness for the specifications of our product when our product is mounted to your product.

All the items and parameters in this product specification/datasheet/catalog have been prescribed on the premise that our product is used for the purpose, under the condition and in the environment specified in this specification. You are requested not to use our product deviating from the condition and the environment specified in this specification.

Please note that the only warranty that we provide regarding the products is its conformance to the specifications provided herein. Accordingly, we shall not be responsible for any defects in products or equipment incorporating such products, which are caused under the conditions other than those specified in this specification.

WE HEREBY DISCLAIMS ALL OTHER WARRANTIES REGARDING THE PRODUCTS, EXPRESS OR IMPLIED, INCLUDING WITHOUT LIMITATION ANY WARRANTY OF FITNESS FOR A PARTICULAR PURPOSE, THAT THEY ARE DEFECT-FREE, OR AGAINST INFRINGEMENT OF INTELLECTUAL PROPERTY RIGHTS.

The product shall not be used in any application listed below which requires especially high reliability for the prevention of such defect as may directly cause damage to the third party's life, body or property. You acknowledge and agree that, if you use our products in such applications, we will not be responsible for any failure to meet such requirements.

SAFFB722MAA0F0A (Band29 (FLO) / Unbalanced / 5pin / 1109)

Important Notice (2/2)

Furthermore, YOU AGREE TO INDEMNIFY AND DEFEND US AND OUR AFFILIATES AGAINST ALL CLAIMS, DAMAGES, COSTS, AND EXPENSES THAT MAY BE INCURRED, INCLUDING WITHOUT LIMITATION, ATTORNEY FEES AND COSTS, DUE TO THE USE OF OUR PRODUCTS IN SUCH APPLICATIONS.

- Aircraft equipment.
- Aerospace equipment
- Undersea equipment.
- Power plant control equipment - Medical equipment.
- Transportation equipment (vehicles, trains, ships, elevator, etc.).
- Traffic signal equipment.
- Disaster prevention / crime prevention equipment.
- Burning / explosion control equipment
- Application of similar complexity and/ or reliability requirements to the applications listed in the above.

We expressly prohibit you from analyzing, breaking, Reverse-Engineering, remodeling altering, and reproducing our product. Our product cannot be used for the product which is prohibited from being manufactured, used, and sold by the regulations and laws in the world.

We do not warrant or represent that any license, either express or implied, is granted under any our patent right, copyright, mask work right, or our other intellectual property right relating to any combination, machine, or process in which our products or services are used. Information provided by us regarding third-party products or services does not constitute a license from us to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from us under our patents or other intellectual property.

Please do not use our products, our technical information and other data provided by us for the purpose of developing of mass-destruction weapons and the purpose of military use.

Moreover, you must comply with "foreign exchange and foreign trade law", the "U.S. export administration regulations", etc.

Please note that we may discontinue the manufacture of our products, due to reasons such as end of supply of materials and/or components from our suppliers.

Customer acknowledges that Murata will, if requested by you, conduct a failure analysis for defect or alleged defect of Products only at the level required for consumer grade Products, and thus such analysis may not always be available or be in accordance with your request (for example, in cases where the defect was caused by components in Products supplied to Murata from a third party).

The product shall not be used in any other application/model than that of claimed to Murata.

Customer acknowledges that engineering samples may deviate from specifications and may contain defects due to their development status.

We reject any liability or product warranty for engineering samples.

In particular we disclaim liability for damages caused by

- the use of the engineering sample other than for evaluation purposes, particularly the installation or integration in the product to be sold by you,
- deviation or lapse in function of engineering sample,
- improper use of engineering samples.

We disclaim any liability for consequential and incidental damages.

If you can't agree the above contents, you should inquire our sales.