




REV.	DATE	DESCRIPTION
A	03/12/03	UPDATE DRAWING FORMAT



RECOMMENDED
CABLE STRIPPING DIM'S



NOTE:
1. CONTACT PIN TO SOLDER

REV.	DATE	DESCRIPTION
A	03/12/03	UPDATE DRAWING FORMAT
8		
7		
6	COVER	BRASS
5	INSULATOR	DELIN
4	CONTACT PIN	BRASS
3	INSULATOR	TEFLON
2	BODY	BER. COPPER
1	HOUSING	BRASS
DESCRIPTION	MATERIAL	FINISH
QTY		
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.		
UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE:		
0.5 - 8mm ± 0.20mm		
8 - 30mm ± 0.40mm		
30 - 120mm ± 0.50mm		
UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE:		
.020 - .315 = ± 0.007"		
.315 - 1.180 = ± 0.015"		
1.180 - 4.724 = ± 0.020"		
DO NOT SCALE DRAWING		
APPROVALS		
DATE		
DRAWN G.R.S.		
03/12/03		
CHECKED		
ISSUED		
SHEET 1 OF 1		
CAD FILE C:/252/252109-75.DWG		
Amphenol Connex		
PART DESCRIPTION		
MCX R/A DIRECT SOLDER PLUG (FOR .085", .086" CABLE)		
PART NO.		
252109-75		
DWG. NO.		
252109-75.DWG		
REV. A		
SIZE A		
SCALE NA		