

## M12 Crimp Slim Design 5pol A-coded male



Image is for illustration purposes only. Please refer to product description.

Part number	21 03 821 1505
Specification	M12 Crimp Slim Design 5pol A-coded male
HARTING eCatalogue	<a href="https://harting.com/21038211505">https://harting.com/21038211505</a>

### Identification

Category	Connectors
Series	Circular connectors M12
Identification	Slim Design
Element	Cable connector
Specification	Straight

### Version

Termination method	Crimp termination
Gender	Male
Shielding	Shielded
Number of contacts	4 5
Coding	A-coding
Locking type	Screw locking
Details	Please order crimp contacts separately.

### Technical characteristics

Conductor cross-section	0.13 ... 0.82 mm <sup>2</sup>
Conductor cross-section [AWG]	AWG 26 ... AWG 18
Wire outer diameter	≤2.3 mm
Rated current	4 A
Rated voltage	48 V AC 60 V DC
Rated impulse voltage	1.5 kV



Pushing Performance  
Since 1945

## Technical characteristics

Pollution degree	3
Overvoltage category	III
Insulation resistance	$>10^8 \Omega$
Contact resistance	$\leq 10 \text{ m}\Omega$
Tightening torque	0.6 Nm
Wrench size (knurled screw / knurled nut)	15
Limiting temperature	-40 ... +85 °C
Mating cycles	$\geq 500$
Degree of protection acc. to IEC 60529	IP65 / IP67 mated condition
Isolation group	I ( $600 \leq \text{CTI}$ )

## Material properties

Material (insert)	Liquid crystal polymer (LCP)
Material (hood/housing)	Zinc die-cast
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08) + A1 (2023-10)
Requirement set with Hazard Levels	R26

## Specifications and approvals

Specifications	IEC 61076-2-101
UL / CSA	UL 2238 CYJV2.E302521 CSA-C22.2 No. 182.3 CYJV8.E302521

## Commercial data

Packaging size	1
Net weight	36.22 g



**Pushing Performance**  
Since 1945

## Commercial data

Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140139572
eCl@ss	27440116 Circular connector (for field assembly)
ETIM	EC002635
UNSPSC 24.0	39121413