




PRODUCT NUMBER	NO. OF POS	DIM K	DIM J	DIM M	DIM H	DIM W	REMARKS
67722-001LF	8	10.01	7.62	5.08	5.44	0.10	NOT TOOLED
67722-002LF	6	7.47	5.08	5.08	5.84	0.10	
67722-003LF	8	10.01	7.62	7.62	5.84	0.10	
67722-103LF	6	7.47	5.08	7.00	5.44	0.10	NOT TOOLED
67722-106LF	12	15.09	12.70	14.59	5.44	0.10	
67722-108LF	16	20.17	17.78	20.03	5.44	0.15	
67722-110LF	20	25.25	22.86	24.90	5.44	0.20	NOT TOOLED






PRODUCT NUMBER
67722-YXXLF

INDICATES THE PRODUCT IS
RoHS COMPLIANT, SEE NOTE 5

DESIGN RIB CODE
0 = STANDARD RIB
1 = LARGE RIB

NOTES:

- MOLDING MATERIAL : POLYAMID (PA 66), COLOR BLACK
25% GLASS FILLED, UL 94 V0
- STANDARD PACKAGING IN POLYBAGS
- TERMINALS MUST BE CRIMPED PROPERLY FOR
SATISFACTORY LATCHING :
 - FOR CRIMPING INSTRUCTIONS, SEE TA-75
 - FOR TERMINAL APPLICATION SEE TA-531.PRODUCT SPECIFICATION: BUS-12-067.
- THIS HOUSING IS INTENDED FOR USE WITH
MINI PV TERMINAL WITH 22-36 GAUGE WIRE
- RoHS COMPLIANT PRODUCT SPECIFICATIONS :
 - MEETS PACKAGING SPECS AS PER GS-14-920
 - PRODUCT MEETS EUROPEAN UNION DIRECTIVES
AND OTHER COUNTRY REGULATIONS AS
DESCRIBED IN GS-22-008.
 - THE PRODUCT IS NOT INTENDED TO BE EXPOSED
TO A MANUFACTURING SOLDER PROCESS.

mat'l. code SEE NOTE 1				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family BERGCON										
ltr	ecn no	dr	date	tolerances unless		otherwise specified		 mm scale 5:1		title MINI LATCH HOUSING DR LATCH										
L	F12-0012	LMU	12.03.13	angles	linear	.X ±0.3														
M	B-14321	LMU	13.03.21			.XX ±0.13														
N	B-18430	LMU	14.07.30			.XXX ±0.05														
				dr	L.MULIN		13.03.21				dwg no				sheet 1 of 1				size	
				engr	L.MULIN		13.03.21				67722				A3					
				chr	J.COMPAGNON		13.03.21													
				appd	LMU		13.03.21													
sheet index		revision sheet																		