



Have a Question?

Chat with a Product
Information Specialist



What can we help you find?



[Products](#)

[Industries](#)

[Resources](#)

[About TE](#)

[Support Center](#)

[My Account](#)


[Home](#) > [Products](#) > [Power Products \(>10 Amps/Contact\)](#) > [Product Feature Selector](#) > Product Details

6450361-1 Product Details

[Share](#)

[Print](#)

[Email](#)



6450361-1

TE Internal Number: 6450361-1

[Active](#)

MULTI-BEAM XL and MULTI-BEAM XLE Connectors

[Always EU RoHS/ELV Compliant](#) (Statement of Compliance)

Product Highlights:

- Product Series = XL
- Board-to-Board
- Connector Assembly
- Connector Style = Receptacle
- Contact Type = Socket

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

[Add to My Part List](#)



[Request Sample](#)



[Find Similar Products](#)



[Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [RIGHT ANGLE RECEPTACLE ASSEMBLY WITH GUIDES MULTI-BE...](#) (PDF, English)

Catalog Pages/Data Sheets:

- [2 PIECE POWER CONNECTORS grq 4-1773458-1](#) (PDF, English)

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Series = XL
- Connector Type = Connector Assembly
- [Mount Angle](#) = Right Angle
- [Termination Style](#) = Solder
- [Mating Type](#) = Blindmate
- [PCB Mount Retention](#) = Without
- Guides = With

Electrical Characteristics:

- Mating Functionality = Standard
- Voltage Rating (Signal) (VAC) = 60
- Voltage Rating (Power) (VDC) = 200

Termination Features:

- Termination Post Length (mm [in]) = 3.43 [0.135]

Body Features:

- [Sequencing](#) = No
- Connector Configuration Orientation = Right-to-Left
- Centerline, DC Module (mm [in]) = 6.35 [0.250]
- Centerline, Matrix (mm [in]) = 2.54 x 2.54 [.100 x .100]

Contact Features:

- Contact Type = Socket
- Contact Material (Power) = High Conductivity Copper
- Contact Material (Signal) = High Conductivity Copper
- Contact Plating, Mating Area, Material = Gold (30)

Housing Features:

- Connector Style = Receptacle
- Housing Material = High Temperature Thermoplastic

Configuration Features:

- [Total Number of DC Power](#) = 6
- [Total Number of AC Power](#) = 0
- Total Number of Coax = 0
- [Total Number of Signal](#) = 24
- Connector Contact Configuration (No. of Pos./Type) = 24/Signal, 6/DC Power

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant

Operation/Application:

- Application Use = Board-to-Board

Other:

- Brand = AMP
- Comment = For additional configurations available, contact Tyco Electronics.

Corporate Information

[Who We Are](#)

[Investors](#)

[News Room](#)

[Supplier Portal](#)

[Careers](#)

Quick Links

[Check Distributor Inventory](#)

[Cross Reference](#)

[Find Documents & Drawings](#)

[Product Compliance Support Center](#)

[Site Map](#)

Customer Support

[Email or Chat With Us](#)

[Find a Phone Number](#)

[Search Knowledge Base](#)

[Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

