








This document is the property of Amphenol Corporation and is delivered on the express condition that it is not to be disclosed, reproduced or used, in whole or in part, for manufacture or sale by anyone other than Amphenol Corporation without its prior consent, & that no right is granted to disclose or to use any information in this document.



RECOMMENDED PANEL CUT-OUT



Customer drawing

POSITION	A	B	C	D	E	F
15	16.92	24.99	39.40	0.25	20.00	28.20
26	25.30	33.32	47.70	0.51	28.00	36.50
44	38.96	47.04	64.50	0.51	41.50	51.00
62	55.42	63.50	80.78	0.51	57.80	67.30

REVISIONS				
SYM	ECN	DESCRIPTION	DATE	APPROVED
1		New release	06/22/10	IP


D-SUB TECHNICAL DATA

SHELL : Steel ,1.25um(50u") min nickel
BODY : Glass filled thermoplastic.
Flame retardant to UL94 V-0 Color ,Black
CONTACTS : Brass,Gold over 50u" min nickel.(According to the P/N)
SCREWLOCK : Steel, 50u" min nickel
REAR INSERT : Brass, 50u" min nickel
O RING: Silicone, Color: Blue
EPOXY: Color: Black
ELECTRICAL : Voltage rating : 300 V RMS at 50 Hz
Current rating : 5A
Insulation resistance >5000 M Ohms
Contact resistance 20mOhms max.
MARKING : Amphenol logo
Manufacturing date(YYWW)



NOTE : Screw L=4.7 For Panel Thickness
Under X=1.2mm
Screw L=5.7 For Panel Thickness
Between X=1.2~2.0mm

PRODUCT CODE



UNLESS OTHERWISE SPECIFIED TOLERANCES		APPROVAL	DATE
U.S.	METRIC	DRAWN Lamon Ho	06/22/10
.X +/-	0.50	CHECKED Lih Wang	06/22/10
.XX +/-	0.30	CHECKED	
.XXX +/-	0.20		
FRACTIONS +/-	2'		
ANGLES +/-			
FOR MATERIALS AND FINISHES SEE NOTES		DRAWING FILE :	
REMOVE SHARP EDGES		ANGLE OF PROJECTION	
DIMENSIONS			
U.S.	INCHES		
METRIC	MM		

Amphenol			Amphenol East Asia Limited
TITLE			
D-sub Waterproof, EHD series male Straight PCB without stand-off or boardlocks type			
SIZE	DRAWING NO.		REV.
A4	C L17EHDXXP1X		1
SCALE	NONE	SHEET 1 OF 1	