
THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 2011
DIFFUSION RESTREINTE LIBRE A LA DIFFUSION
© COPYRIGHT - 2011 ALL RIGHTS RESERVED. TOUS DROITS RESERVES


LOC	DIST
F	00


REVISIONS

P	LTR	DESCRIPTION MODIFICATIONS	DATE	DWN DESS.	APVD APP.
	A	FIRST ISSUE	13SEP2007	PFs	JDr
	B	ADD NG9K SEALS, HEAD FORMS SET UP.	19SEP2008	PFs	JDr
	C	SET UP DIM 31, 33, 34 AND 35.	17JUN2011	PFs	JDr
	D	SET UP DIM 21	15SEP2011	PFs	JDr




COUPE C-C
SECTION C-C







COUPE D-D
SECTION D-D




COUPE E-E
SECTION E-E






LARGEUR ENTREFER REGLER POUR DES LANGUETTES DE 1mm
WIDTH GAP FOR 1mm TAB

ECHELLE 1:1
SCALE 1:1





NOTA		NOTES	
1	(X) = POUR INFORMATION	1	*(X) = FOR INFORMATION*
2	CONDITIONNEMENT : VOIR SPECIFICATION 107-15602	2	*PACKAGING : SEE SPECIFICATION 107-15602*

PRODUIT ASSOCIE / *APPLIED PRODUCT*

DESIGNATION DES JOINTS *SEALS DESCRIPTION*	REFERENCE *TE PN*	REFERENCE *CUSTOMER PN*	COULEUR *COLOR*
JOINT UNIFILAIRE 7 A 10 MM2 *SINGLE WIRE SEAL 7 TO 10 MM2*	1544316-2		ORANGE / *ORANGE*
SUPER JOINT UNIFILAIRE 7 A 10 MM2 *SUPER SINGLE WIRE SEAL 7 TO 10 MM2*	1544664-2		ORANGE / *ORANGE*
JOINT UNIFILAIRE NG9K 6 A 7 MM2 *NG9K SINGLE WIRE SEAL 6 TO 7 MM2*	1544970-2		BLEU / *BLUE*
JOINT UNIFILAIRE NG9K 10 MM2 *NG9K SINGLE WIRE SEAL 10 MM2*	1544970-3		JAUNE / *YELLOW*
INTERFACE MONTABILITE / *INTERFACE CAVITY*			
1544953			

REFERENCE *TE PN*	REFERENCE CLIENT *CUSTOMER PN*	Y : REPERE MATIERE *MATERIAL REPERE*	MATIERE *MATERIAL*	TRAITEMENT DE SURFACE *HEAT TREATMENT*
1544966-1		S	CuNiSi SELON SPECIFICATION: 100-1230 *CuNiSi ACCORDING TO SPECIFICATION: 100-1230*	PRE-ETAME SnAg DE 1 A 3µ SELON SPECIFICATION 112-73-2 *PRE-TINNED SnAg FROM 1 TO 3µ ACCORDING SPECIFICATION 112-73-2*
1544966-2		T		PRE-ARGENTE Ag DE 1 A 3µ SELON SPECIFICATIONS 212-7, 112-32 ET 118-91 *PRE-SILVERED Ag FROM 1 TO 3µ ACCORDING SPECIFICATIONS 212-7, 112-32 AND 118-91*

THIS DRAWING IS A CONTROLLED DOCUMENT.
CE PLAN EST UN DOCUMENT CONTROLE PAR AMP INCORPORATED.
IL EST SUSCEPTIBLE D'ETRE REVISE, CONTACTER LE SERVICE TECHNIQUE D'AMP DE FRANCE POUR OBTENIR LA DERNIERE REVISION.

DIMENSIONS: mm
TOLERANCES UNLESS OTHERWISE SPECIFIED: TOLERANCES NON SPECIFIEES (SAUF NB DE DECIMALES)
0 PLC/DEC: ±.
1 PLC/DEC: ±.
2 PLC/DEC: ±0.1
3 PLC/DEC: ±.
4 PLC/DEC: ±.
ANGLES ±2°
MATERIAL MATIERE: SEE TABLE
FINISH FINITION: SEE TABLE

DWN/DESSINE P. FLORES 13SEP07
CHK/VERIFIE F. SAPET 13SEP07
APVD/APROUVE I. DAHER 13SEP07
PRODUCT SPEC SPEC. PRODUIT 108-15382
APPLICATION SPEC SPEC. APPLICATION 114-15107
WEIGHT MASSE APPROX. 0.0023kg

TE Connectivity

NAME TITRE
8mm NG1+ FEMALE TERMINAL
WIRE SIZE 7-10 SQUARE MM

SIZE FORMAT A2 | CAGE CODE 00779 | DRAWING NO No PLAN C-1544966 | RESTRICTED TO RESERVE A -
CUSTOMER DRAWING /PLAN CLIENT UNIQUEMENT POUR REFERENCE | SCALE ECHELLE 5:2 | SHEET FEUILLE 1 OF DE 1 | REV D

1471-9 (3/11)

Downloaded from Arrow.com.