




SEK 20P female connector

SEK 20P female connector

TOLERANCE FOR "L" LENGTH

Part-No.	Length-L
33 18 243 150 0068	1500mm
33 18 243 100 0062	1000mm
33 18 243 050 0060	500mm

NOTES:

- 1.) CABLE MUST BE PERFORMED 100% CONTINUITY TEST.
- 2.) WHITE LABEL CONTENT:

CMK/YR-XXXXX-X-XX
HARTING P/N

BLACK FONT; FONT HEIGHT: 3.5.

3.) CABLE SHOULD BE FOLDED MANY CIRCLES ACCORDING TO TOTAL CABLE LENGTH AND PACKED BY A PLASTIC BAG (QTY ACCORDING TO ACTUAL CONDITION),STICK THE LABEL WITH P/N,QTY AND LOT NUMBER ON IT,THEN PUT IT INTO THE CARTON (QTY ACCORDING TO ACTUAL CONDITION).

4.) THE CARTON SHOULD BE STICKED THE LABEL WITH P/N AND QTY CONTENT.

 All Dimensions in mm Original Size DIN A 3			Techn. Character.			Free size tolerances		
			Date	Name	Scale			
			Detail	11.08.08	Andrew.H	/		
			Insp.					
			Stand					
			ZHUHAI HARTING LIMITED 			TB 33 18 0003 .00		
Mod.	Date	Name				Page /		