

PRO PM 75W 48V 1.6A**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Due to the wide range of variants with output voltages of 5, 12, 24, and 48 V and extensive international approvals, they are suitable for use in many applications. The power range extends from 35 W to 350 W. The individual adaptability makes PRO-PM the right choice for many standard machines.

General ordering data

| | |
|------------|---|
| Version | Power supply, switch-mode power supply unit |
| Order No. | 2660200284 |
| Type | PRO PM 75W 48V 1.6A |
| GTIN (EAN) | 4050118782059 |
| Qty. | 1 items |

PRO PM 75W 48V 1.6A

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

| | | | |
|------------|-------|-----------------|-------------|
| Depth | 99 mm | Depth (inches) | 3.8976 inch |
| Height | 30 mm | Height (inches) | 1.1811 inch |
| Width | 97 mm | Width (inches) | 3.8189 inch |
| Net weight | 240 g | | |

Temperatures

| | | | |
|---------------------|----------------|-----------------------|----------------|
| Storage temperature | -40 °C...85 °C | Operating temperature | -20 °C...70 °C |
| Humidity | 5...95 % RH | | |

Environmental Product Compliance

| | |
|--------------------------------------|---|
| RoHS Compliance Status | Compliant with exemption |
| RoHS Exemption (if applicable/known) | 6c, 7a, 7cl |
| REACH SVHC | Lead 7439-92-1, Lead monoxide 1317-36-8 |
| SCIP | 015c3a09-4dd7-4b84-85e2-16a46fa4e79a |

Input

| | | | |
|--|---|-------|--|
| Connection system | Screw connection | | |
| AC input voltage range | 90...264 V AC | | |
| Recommended back-up fuse | 4 A at 230 V AC, characteristic curve C | | |
| Frequency range AC | 47...63 Hz | | |
| Rated input voltage | 100...240 V AC | | |
| AC current consumption | 1 A @ 230 V AC / 2 A @ 115 V AC | | |
| Inrush current | max. 45 A | | |
| Current consumption in relation to the input voltage | Voltage type | AC | |
| | Input voltage | 230 V | |
| | Input current | 1 A | |
| | Voltage type | AC | |
| | Input voltage | 115 V | |
| | Input current | 2 A | |
| Nominal power consumption | 87.2 VA | | |

Output

| | | | |
|----------------------------------|---|--------------------------------|------------------------|
| Output power | 75 W | Mains failure bridge-over time | 20 ms |
| Connection system | Screw connection | Rated output voltage | 48 V DC |
| Residual ripple, breaking spikes | <150 mVPP | Parallel connection option | Yes, with diode module |
| Overload protection | 120%...180% Inominal, hiccup mode with automatic recovery | Surge protection | 55...62 V @ 48 V DC |
| Output voltage, note | ± 10% nominal output voltage tolerance, adjustable with potentiometer | Rated current | 1.6 A |

PRO PM 75W 48V 1.6A

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

General data

| | | | |
|--|------------------------|-------------------|-------------------|
| Degree of efficiency | 86% | Humidity | 5...95 % RH |
| Protection degree | IP20 | Status indication | LED green: ready |
| Mounting position, installation notice | Panel mount, screw fix | Derating | > 50°C (2% / 1°C) |
| Short-circuit protection | Yes | | |

EMC / shock / vibration

| | | | |
|------------------------------------|--|---|---|
| Shock resistance IEC 60068-2-27 | 30 g in all directions | Noise emission in accordance with EN55032 | Class B |
| Interference immunity test acc. to | Burst: EN 61000-4-4 / ESD EN 61000-4-2, EN61000-4-3 (HF field), EN 61000-4-5 (surge), EN 61000-4-6 (conducted), EN61000-4-8 (Fields), EN 61000-4-11 (Dips) | Vibration resistance IEC 60068-2-6 | 10...500 Hz, constant acceleration 5 g, 10 minutes/cycle, 60 minutes/axis |

Insulation coordination

| | | | |
|-----------------------------------|--------|----------------------------------|------|
| Insulation voltage, input/output | 3 kV | Insulation voltage input / earth | 2 kV |
| Insulation voltage output / earth | 0.5 kV | | |

Electrical safety (applied standards)

| | | | |
|--------------------------|--|--|--|
| Safety extra-low voltage | SELV acc. to IEC 60950-1, PELV according to EN 60204-1 | | |
|--------------------------|--|--|--|

Connection data (input)

| | | | |
|---|----------------------|---|-------------------|
| Connection system | Screw connection | Conductor cross-section, AWG/kcmil , max. | 12 AWG |
| Conductor cross-section, AWG/kcmil , min. | 21 AWG | Conductor cross-section, rigid , max. | 4 mm ² |
| Conductor cross-section, rigid , min. | 0.34 mm ² | | |

Connection data (output)

| | | | |
|---|----------------------|---|-------------------|
| Connection system | Screw connection | Conductor cross-section, AWG/kcmil , max. | 12 AWG |
| Conductor cross-section, AWG/kcmil , min. | 21 AWG | Conductor cross-section, rigid , max. | 4 mm ² |
| Conductor cross-section, rigid , min. | 0.34 mm ² | | |

Signalling

| | | | |
|-------------------|------------------|--|--|
| Status indication | LED green: ready | | |
|-------------------|------------------|--|--|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC002540 | ETIM 9.0 | EC002540 |
| ETIM 10.0 | EC002540 | ECLASS 14.0 | 27-04-07-01 |
| ECLASS 15.0 | 27-04-07-01 | | |