





REV.	DATE	DESCRIPTION
A	02/24/04	UPDATE DRAWING FORMAT



RECOMMENDED CABLE
STRIPPING DIMENSIONS



8					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020"	APPROVALS	DATE	Amphenol Connex														
7						DRAWN	G.R.S.						02/24/04									
6						CHECKED			PART DESCRIPTION MCX CRIMP PLUG (FOR RG-174/U, 188A/U, 316/U)													
5						ISSUED																
4	FERRULE	COPPER	NICKEL	1		SHEET	1 OF 1		PART NO. 252101													
3	CONTACT PIN	BRASS	GOLD	1																		
2	INSULATOR	TEFLON	NATURAL	1				DWG. NO. 252101.DWG														
1	BODY	BER. COPPER	NICKEL	1																		
DESCRIPTION					MATERIAL	FINISH	QTY	DO NOT SCALE DRAWING					CAD FILE	C:/252/252101.DWG			REV.	A	SIZE	A	SCALE	NA