





MATERIAL NUMBER	ENGINEERING NUMBER	CARRIER	TAB THICKNESS	LOGO ORIENTATION	REEL CENTER HOLE Ø REF.
197084023	19708-4023	STRIP	.020/0.51	IN	.750/19.05
197084033	19708-4033	STRIP	.032/0.81	IN	1.250/31.75



RECOMMENDED PCB HOLE LAYOUT



- NOTES:
1. BARE EDGES PERMISSIBLE AT CARRIER CUT OFF.
 2. MATERIAL: BRASS C26000
 3. MATERIAL THICKNESS: SEE CHART
 4. TAB CONFORMS TO NEMA SPECIFICATIONS.
 5. ALL DIMENSIONS AND NOTES REFERENCE UNLESS OTHERWISE NOTED.
 6. PLATING: MATTE TIN, 150µ IN/3.81µmm MINIMUM THICKNESS OVER NICKEL 50µ IN/1.25µmm MINIMUM THICKNESS.
 7. REF.: 10,000 MINIMUM PARTS PER REEL, REEL HAS 24" DIAMETER REEL WITH A (SEE CHART) DIAMETER CENTER HOLE.
 8. PART IS ROHS COMPLIANT.

ADDED LOGO OPTIONS & ROHS EC NO: ETC2007-0338 DRAWN BY: DRWNEHLE 2007/03/15 CHKD: JMACNEIL 2007/03/26 APPR: JMACNEIL 2007/03/27	DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE IN/MM		SCALE 4:1	DESIGN UNITS INCH	 THIRD ANGLE PROJECTION			
			mm		INCH		DRAWN BY DATE		TITLE QUICK DISCONNECT, PCB MOUNT, .187 X .032/.020 TAB W/STABILIZERS MOLEX INCORPORATED				
			4 PLACES ± --- ± ---		JPAWLICK 01/06/14								
			3 PLACES ± --- ± .005		CHECKED BY DATE								
			2 PLACES ± 0.13 ± .01		RDEROSS 01/06/15								
			1 PLACE ± 0.25 ± ---		APPROVED BY DATE								
			ANGULAR ± 1 °		RDEROSS 01/06/15		 MOLEX INCORPORATED						
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		MATERIAL NO.				DOCUMENT NO.		SHEET NO.		
					SEE CHART				SD-19708-001		1 OF 1		
			SIZE		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION								