



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	22JUN2015	DL	CW
	A1	ECR-17-018760	290EC2017	CH	CW
	B	ECR-20-008190	14SEP2020	WQR	CW

注：
1、技术参数：
主体材料： 铝合金
表面处理： 灰色粉末喷涂
防护等级： IP65（配合）



Technical drawing of the front view of a rectangular metal plate. The drawing shows a central rectangular area with rounded corners, surrounded by a border. The overall width is dimensioned as 61.9 and the overall height as 24.9. There are four circular holes, one in each corner, with a diameter dimensioned as 4X R5. The drawing includes a center line and a dashed line indicating the internal rectangular area.

TYPE 2: HIGH CONSTRUCTION + STAINLESS STEEL
DOUBLE LOCKING, SIDE ENTRY + BOTTOM CUT OUT,
OTHER SPEC REFER TO TYPE 1.
类型 2: 高结构 + 不锈钢双扣, 侧出 + 底部开孔, 其它参照类型 1。

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 22JUN2015 DAVID.LI CHK 22JUN2015 CHRIS.WANG APVD 22JUN2015 XIANG.XU		 TE Connectivity			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		NAME H16B-SGRHS-PG/M			
		PRODUCT SPEC 108-137013 APPLICATION SPEC 114-137013		SIZE A2		CAGE CODE -	
MATERIAL - -		FINISH - -		DRAWING NO C=TI47016XXXX000		RESTRICTED TO	
CUSTOMER DRAWING				SCALE 1:1		SHEET 1 of 3	
						REV B	





D

C



B

A

printed on 14 Apr 2021 13:16 (China Standard Time) from TE343646



TYPE 3: HIGH CONSTRUCTION + METAL DOUBLE LOCKING,
SIDE ENTRY, OTHER SPEC REFER TO TYPE 1.
类型3: 高结构+彩锌双扣, 侧出, 其它参照类型1.



SCALE 1:2

NOTES:
SEE SHEET 1

D

C

B

A

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DAVID.LI 22JUN2015	TE Connectivity		
DIMENSIONS: mm		CHK CHRIS.WANG 22JUN2015			
		APVD XIANG.XU 22JUN2015	NAME HI6B-SGRHS-PG/M		
		PRODUCT SPEC 108-137013	SIZE A2		
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±- 4 PLC ±- ANGLES ±- FINISH		APPLICATION SPEC 114-137013	CAGE CODE -	DRAWING NO C-TI47016XXXX000	RESTRICTED TO
MATERIAL - -		WEIGHT -	SCALE 1:2		
CUSTOMER DRAWING			SHEET 2	OF 3	REV B

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

NOTES:

SEE SHEET 1

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

T1470162232-000	H16B-SGRH-2M32	H16B HOUSING, SURFACE MOUNTED, METAL DOUBLE LOCKING, 2M32, HIGH CONSTRUCTION, POWDER COATED, GREY H16B下壳, 表面安装, 彩锌双扣, 2M32, 高结构, 灰色粉末喷涂	M32	M32	TYPE 3 类型 3
T1470162229-000	H16B-SGRH-2PG29	H16B HOUSING, SURFACE MOUNTED, METAL DOUBLE LOCKING, 2PG29, HIGH CONSTRUCTION, POWDER COATED, GREY H16B下壳, 表面安装, 彩锌双扣, 2PG29, 高结构, 灰色粉末喷涂	PG29	PG29	
T1470162225-000	H16B-SGRH-2M25	H16B HOUSING, SURFACE MOUNTED, METAL DOUBLE LOCKING, 2M25, HIGH CONSTRUCTION, POWDER COATED, GREY H16B下壳, 表面安装, 彩锌双扣, 2M25, 高结构, 灰色粉末喷涂	M25	M25	
T1470162221-000	H16B-SGRH-2PG21	H16B HOUSING, SURFACE MOUNTED, METAL DOUBLE LOCKING, 2PG21, HIGH CONSTRUCTION, POWDER COATED, GREY H16B下壳, 表面安装, 彩锌双扣, 2PG21, 高结构, 灰色粉末喷涂	PG21	PG21	
T1470162132-000	H16B-SGRH-M32	H16B HOUSING, SURFACE MOUNTED, METAL DOUBLE LOCKING, M32,HIGH CONSTRUCTION, POWDER COATED, GREY H16B下壳, 表面安装, 彩锌双扣, M32, 高结构, 灰色粉末喷涂	M32	-	
T1470162129-000	H16B-SGRH-PG29	H16B HOUSING, SURFACE MOUNTED, METAL DOUBLE LOCKING, PG29,HIGH CONSTRUCTION, POWDER COATED, GREY H16B下壳, 表面安装, 彩锌双扣, PG29, 高结构, 灰色粉末喷涂	PG29	-	
T1470162125-000	H16B-SGRH-M25	H16B HOUSING, SURFACE MOUNTED, METAL DOUBLE LOCKING, M25,HIGH CONSTRUCTION, POWDER COATED, GREY H16B下壳, 表面安装, 彩锌双扣, M25, 高结构, 灰色粉末喷涂	M25	-	
T1470162121-000	H16B-SGRH-PG21	H16B HOUSING, SURFACE MOUNTED, METAL DOUBLE LOCKING, PG21,HIGH CONSTRUCTION, POWDER COATED, GREY H16B下壳, 表面安装, 彩锌双扣, PG21, 高结构, 灰色粉末喷涂	PG21	-	TYPE 2 类型2
T1470165121-000	H16B-SGRHS-PG21	H16B HOUSING, SURFACE MOUNTED, STAINLESS STEEL DOUBLE LOCKING, PG21, HIGH CONSTRUCTION, MILL ON BOTTOM, POWDER COATED, GREY H16B下壳, 表面安装, 不锈钢双扣, PG21, 高结构, 底部铣槽, 灰色粉末喷涂	PG21	-	
T1470161232-000	H16B-SGRHS-2M32	H16B HOUSING, SURFACE MOUNTED, STAINLESS STEEL DOUBLE LOCKING, 2M32, HIGH CONSTRUCTION, POWDER COATED, GREY H16B下壳, 表面安装, 不锈钢双扣, 2M32, 高结构, 灰色粉末喷涂	M32	M32	TYPE 1 类型1
T1470161229-000	H16B-SGRHS-2PG29	H16B HOUSING, SURFACE MOUNTED, STAINLESS STEEL DOUBLE LOCKING, 2PG29, HIGH CONSTRUCTION, POWDER COATED, GREY H16B下壳, 表面安装, 不锈钢双扣, 2PG29, 高结构, 灰色粉末喷涂	PG29	PG29	
T1470161221-000	H16B-SGRHS-2PG21	H16B HOUSING, SURFACE MOUNTED, STAINLESS STEEL DOUBLE LOCKING, 2PG21, HIGH CONSTRUCTION, POWDER COATED, GREY H16B下壳, 表面安装, 不锈钢双扣, 2PG21, 高结构, 灰色粉末喷涂	PG21	PG21	
T1470161140-000	H16B-SGRHS-M40	H16B HOUSING, SURFACE MOUNTED, STAINLESS STEEL DOUBLE LOCKING, M40, HIGH CONSTRUCTION, POWDER COATED, GREY H16B下壳, 表面安装, 不锈钢双扣, M40, 高结构, 灰色粉末喷涂	M40	-	
T1470161132-000	H16B-SGRHS-M32	H16B HOUSING, SURFACE MOUNTED, STAINLESS STEEL DOUBLE LOCKING, M32, HIGH CONSTRUCTION, POWDER COATED, GREY H16B下壳, 表面安装, 不锈钢双扣, M32, 高结构, 灰色粉末喷涂	M32	-	
T1470161129-000	H16B-SGRHS-PG29	H16B HOUSING, SURFACE MOUNTED, STAINLESS STEEL DOUBLE LOCKING, PG29, HIGH CONSTRUCTION, POWDER COATED, GREY H16B下壳, 表面安装, 不锈钢双扣, PG29, 高结构, 灰色粉末喷涂	PG29	-	
T1470161121-000	H16B-SGRHS-PG21	H16B HOUSING, SURFACE MOUNTED, STAINLESS STEEL DOUBLE LOCKING, PG21, HIGH CONSTRUCTION, POWDER COATED, GREY H16B下壳, 表面安装, 不锈钢双扣, PG21, 高结构, 灰色粉末喷涂	PG21	-	
T1470160000-000	H16B-SGRHS-T	H16B HOUSING, SURFACE MOUNTED, STAINLESS STEEL DOUBLE LOCKING, NO ENTRY, HIGH CONSTRUCTION, POWDER COATED, GREY H16B下壳, 表面安装, 不锈钢双扣, 不开孔, 高结构, 灰色粉末喷涂	-	-	
PART NUMBER 料号	PART DESCRIPTION 描述	PG/M THREAD 1 PG/M 螺纹孔1		PG/M THREAD 2 PG/M 螺纹孔2	TYPE 类型

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±-

1 PLC ±-

2 PLC ±-

3 PLC ±-

4 PLC ±-

ANGLES ±-

FINISH -

-

DWN DAVID.LI 22JUN2015

CHK CHRIS.WANG 22JUN2015

APVD XIANG.XU 22JUN2015

PRODUCT SPEC 108-137013

APPLICATION SPEC 114-137013

WEIGHT -

CUSTOMER DRAWING

TE Connectivity

NAME H16B-SGRHS-PG/M

SIZE A2

CAGE CODE -

DRAWING NO T147016XXXX000

RESTRICTED TO

SCALE 1:1

SHEET 3 OF 3

REV B

1471-9 (3/13)

1471-9 (3/13)

1471-9 (3/13)

1471-9 (3/13)

printed on 14 Apr 2021 13:16 (China Standard Time) from TE343646

Downloaded from Arrow.com