



Part Number : [02081001](#)

Product Description : MLX Female Crimp Terminal, 20-14 AWG, Brass, Tin (Sn) Plating, Reel

Series Number : 42024

Status : Active

Product Category : Crimp Terminals

Engineering Part Number : 42024-1A1

Packaging Alternative : [02081002](#) (Bag)



Documents and Resources

Drawings

[002081001_sd.pdf](#)

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)


Specifications

[PS-42022-0001-001.pdf](#)

[TS-42022-0001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	 per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Terminals
Series	42024
Description	MLX Female Crimp Terminal, 20-14 AWG, Brass, Tin (Sn) Plating, Reel
Application	Power, Wire-to-Board, Wire-to- Wire
Product Name	MLX
UPC	800753615878

Physical

Gender	Female
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.406/g
Packaging Type	Reel
Plating min - Mating	0.508µm
Plating min - Termination	0.508µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.52-3.30mm
Wire Size (AWG)	14, 16, 18, 20
Wire Size mm ²	N/A

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Application Tooling

Global

Description	Part Number
Extraction Tool for MLX 2.13mm Diameter Pin and Socket Crimp Terminals	<u>11010168</u>
PremiumGrade Hand Crimp Tool for MLX Pin and Socket Terminals, 20-14 AWG	<u>638116800</u>
FineAdjust Applicator for Crimp Terminals, 20-14 AWG Wire with 2.08-2.50mm Diameter Insulation	<u>639007500</u>
FineAdjust Applicator for Crimp Terminals, 20-14 AWG Wire with 2.65-3.30mm Diameter Insulation	<u>639009800</u>
FineAdjust Applicator for Crimp Terminals, 20-14 AWG Wire with 2.41-2.95mm Diameter Insulation	<u>639009900</u>

This document was generated on Apr 24, 2026