




SHELL SIZE	SHELL SIZE CODE	A MAX	B MAX	C	D	E	F	H	J MIN	K MAX	L MIN	M	N ±6.35
11	B	35,05	20,15	12,93 - 12,77	14,99 - 14,89	16,26 - 16,16	17,15 - 16,99	7,02 - 6,85	10,74	27,00	18,00	20,50 - 18,00	127,00
13	C	39,88	23,35	16,10 - 19,54	18,32 - 18,22	19,33 - 19,23	17,15 - 16,99	7,02 - 6,85	13,63	30,00	20,00	27,00 - 20,00	127,00
15	D	42,17	26,52	19,28 - 19,12	21,47 - 21,37	22,48 - 22,38	17,15 - 16,99	7,02 - 6,85	16,81	31,00	23,00	22,50 - 18,00	127,00
17	E	45,47	29,72	22,48 - 22,32	24,64 - 24,54	25,66 - 25,56	17,15 - 16,99	7,02 - 6,85	19,98	37,00	26,00	30,50 - 23,50	127,00
19	F	48,77	32,87	25,63 - 25,47		27,67 - 27,57	16,90 - 16,73	6,76 - 6,60	22,25	40,00	29,00	31,50 - 25,00	127,00
21	G	52,33	36,05	28,80 - 28,64		30,84 - 30,74	16,90 - 16,73	6,76 - 6,60	25,42	44,00	32,00	33,00 - 26,50	127,00
23	H	57,15	39,22	31,98 - 31,82		34,12 - 34,02	16,90 - 16,73	6,76 - 6,60	28,60	46,00	34,00	34,00 - 27,50	127,00
25	J	60,45	42,40	35,15 - 35,00		37,34 - 37,24	16,90 - 16,73	6,76 - 6,60	31,77	49,00	39,00	38,00 - 30,00	127,00

PC451-15-1-C-N

CODE	MATERIAL / FINISH
1-C	ALUMINIUM / ELECTROLESS NICKEL
1-B	ALUMINIUM / CADMIUM OLIVE DRAB OVER ELECTROLESS NICKEL
1-ZB	ALUMINIUM / ZINC COBALT OLIVE DRAB OVER ELECTROLESS NICKEL
1-ZK	ALUMINIUM / ZINC COBALT BLACK OVER ELECTROLESS NICKEL
1-ZN	ALUMINIUM / ZINC NICKEL BLACK PASSIVATE OVER ELECTROLESS NICKEL
4-J	STAINLESS STEEL / PASSIVATE
2-Z	NICKEL ALUMINIUM BRONZE / SHOT BLAST

LIST NOT EXHAUSTIVE, FOR COMPREHENSIVE LIST AND SPECS, SEE WEBSITE

SERIES _____
SHELL SIZE _____
MATERIAL - SEE TABLE _____
FINISH - SEE TABLE _____
LANYARD STYLE _____
R - ROPE AND EYELET
N - ROPE AND RING


PART NUMBER FOR
ALTERNATIVE LANYARD/ATTACHMENT OPTIONS

PC451-15-1-C-WR4-17

SERIES _____
SHELL SIZE _____
MATERIAL - SEE TABLE _____
FINISH - SEE TABLE _____
LANYARD STYLE (SEE NOTE 2) _____
LANYARD LENGTH (IN INCHES) _____
+1.0"/0" TOLERANCE
ATTACHMENT STYLE (SEE NOTE 2) _____

- NOTES :
1. DIMENSIONS ARE IN MILLIMETERS
 2. SEE P11078 FOR ALTERNATIVE LANYARD/ATTACHMENT OPTIONS

MATERIALS
COVER - SEE TABLE
RING - STAINLESS STEEL, PASSIVATED, 1,02 MILLIMETERS MAXIMUM THICKNESS
ROPE - INSULATED STAINLESS STEEL, PASSIVATED
FASTENER - STAINLESS STEEL, PASSIVATED

DRAWN		DATE		 3RD ANGLE PROJECTION NOT TO SCALE	PART NUMBER:					 Polamco	
N.HAWKINS		24/09/2018			PC451 SERIES						
DESIGN APPROVAL		DATE			TITLE:						
M.PAUL		28/11/2016			PLUG PROTECTIVE COVER						
DOC TYPE		Customer Drawing			UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS IN MILLIMETRES GENERAL TOL LINEAR +/- 0,25MM ANGULAR +/- 1°	ASSY USED ON: MIL-DTL-38999/51					 TE connectivity
ISSUE/REV		DCR				THIS DRAWING IS COPYRIGHT AND THE PROPERTY OF POLAMCO LTD IT MUST NOT BE COPIED, USED FOR MANUFACTURE OR OTHERWISE DISCLOSED WITHOUT PRIOR WRITTEN CONSENT OF THE COMPANY.					
AC		---									
NCAGE CODE U5792		WEIGHT		MATERIAL SEE PART NUMBER BREAKDOWN	POLAMCO LTD, WESTON LOCK, LOWER BRISTOL ROAD BATH BA2 1EP		SHT 1	DRAWING NO: C5877			
		N/A			FINISH SEE PART NUMBER BREAKDOWN						