


ΔF

PANDUIT PART NUMBER	 "X" 	 "X" TOL.	 "T" 	 "T" TOL.	 "R" 	 "R" TOL.	LENGTH	WEIGHT
D2H6	1.79 (45.3)	±.03 (.8)	.07 (1.7)	±.012 (.3)	.24 (6.0)	±.03 (.8)	72.00 in	.096 LB/FT (.143 Kg/M)
D3H6	2.74 (69.7)	±.05 (1.3)	.09 (2.2)	±.016 (.4)	.26 (6.5)	±.03 (.8)	±.13 in	.165 LB/FT (.245 Kg/M)
D4H6	3.53 (89.8)	±.06 (1.5)	.11 (2.8)	±.020 (.5)	.26 (6.5)	±.03 (.8)	(1829mm ±3.3mm)	.285 LB/FT (.426 Kg/M)

1. SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. THIS PART IS INTENDED TO BE USED WITH MOUNTING BASE DB-C IN ORDER TO SUCCEED AS A DIVIDER WALL APPLICATION.
3. DIMENSIONS IN PARENTHESIS ARE IN METRIC.



										CAD FILENAME/LAYERS		D34301_DC_DH6_F_DIV_03A.prt	
										PANDUIT CORP. TINLEY PARK, ILLINOIS SOLID DIVIDER WALL FOR WIRING DUCT & FIBER DUCT(D2H6, D3H6, D4H6) CUSTOMER DRAWING			
4	5/24/10	LEF	MKBE	F.REMOVED PARTS D1H6 & D1.5H6	34301-05	MKBE	MKBE						
3	4/14/04	UCST	JKG	E. MODIFIED DIM."X" & "R" IN VIEW AND CHART D. MODIFIED TITLE	34301-05	HIW	HIW			UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ± (.XX) ±.06 (1.5) ANGLES ±		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
2	3-11-94	DW	CEF	C. REV'D DIM "T" AND ADDED DIM "R".	34301-05	CEF	CEF						
1	1-28-94	DW	CEF	B. REVISED DIMENSIONS. A. ADDED TOLERANCES.	34301-05	CEF				DRAWN BY DW	MAT'L: PVC	SCALE NONE	
R	5-5-93	DW	KRKE	RELEASED TO PRODUCTION	34301-05	CEF				DATE 5-5-93		DRAWING NO. 34301-05	DWG A
REV	DATE	BY	CHK	DESCRIPTION	ECN	-	R	CUST	SUP	CHK'D KRKE		SIZE	