



(Standard)



(Optional)


 ANSI/AAMI ES60601-1 BS EN/EN60601-1 IEC60601-1 TPT004
 (except -C type)


(G model)


■ Features

- 5"×3" compact size
- Medical safety approved (2 x MOPP) according to ANSI/AAMI ES60601-1 and IEC/BS EN/EN 60601-1
- Suitable for BF application with appropriate system consideration
- 100W convection, 145W force air
- EMI Class B for Class I configuration
- No load power consumption<0.75W by PS-ON control (G model)
- Extremely low leakage current
- 5Vdc standby output, Power Good, Power Fail
- Protections: Short circuit / Overload / Over voltage / Over temperature
- Lifetime > 85K hours
- 3 years warranty

■ Description

RPT(G)-160 is a 145W highly reliable PCB type medical power supply with a high power density on the 5" by 3" footprint. It accepts 90~264VAC input and offers triple output voltages. The extremely low leakage current is less than 160 μ A. In addition, it conforms to international medical regulations (2*MOPP) and EMC BS EN/EN55011, perfectly fitting all kinds of BF rated "patient contact" medical system equipment. RPT(G)-160 series also offers the enclosed style model [RPT(G)-160-C].

■ Model Encoding



Type	Description	Note
Blank	PCB Type	In Stock
C	Enclosed casing type	Optional




SPECIFICATION for PCB Type(standard)

MODEL	RPT(G)-160A			RPT(G)-160B			RPT(G)-160C			RPT(G)-160D																	
OUTPUT	OUTPUT NUMBER	CH1	CH2	CH3	CH1	CH2	CH3	CH1	CH2	CH3	CH1	CH2															
	DC VOLTAGE	5V	12V	-5V	5V	12V	-12V	5V	15V	-15V	5V	12V															
	RATED (20.5CFM)	14A	5.5A	1A	14A	5A	1A	14A	3.6A	1A	11A	5A															
	CURRENT RANGE (20.5CFM)	0.6 ~ 14A	0.2 ~ 5.5A	0.1 ~ 1A	0.6 ~ 14A	0.2 ~ 5A	0.1 ~ 1A	0.6 ~ 14A	0.1 ~ 3.6A	0.1 ~ 1A	0.3 ~ 11A	0.2 ~ 5A															
	RANGE (convection)	0.6 ~ 9A	0.2 ~ 3.8A	0.1 ~ 0.6A	0.6 ~ 9A	0.2 ~ 3.4A	0.1 ~ 0.8A	0.6 ~ 9A	0.1 ~ 2.6A	0.1 ~ 0.8A	0.3 ~ 8A	0.2 ~ 2.6A															
	RATED POWER	20.5CFM Note.2	145W		146W		143W		147.8W																		
	Convection Note.3	98.6W			98.4W		99W		98.2W																		
	RIPPLE & NOISE (max.) Note.4	60mVp-p	80mVp-p	120mVp-p	60mVp-p	100mVp-p	100mVp-p	60mVp-p	80mVp-p	100mVp-p	80mVp-p	100mVp-p															
	VOLTAGE ADJ. RANGE	CH1:5 ~ 5.5V																									
	VOLTAGE TOLERANCE Note.5	±2.0%	±5.0%	-5,+7%	±2.0%	±5.0%	-4,+5%	±2.0%	±4.0%	±8.0%	±2.0%	±5.0%															
INPUT	LINE REGULATION	±0.5%	±1.0%	±1.0%	±0.5%	±1.0%	±1.0%	±0.5%	±1.0%	±1.0%	±0.5%	±1.0%															
	LOAD REGULATION	±1.5%	±3.0%	-5,+6%	±1.5%	±3.0%	-4,+5%	±2.0%	±3.0%	±8.0%	±1.5%	±3.0%															
	SETUP, RISE TIME	1800ms, 30ms/230VAC			3500ms, 30ms/115VAC at full load																						
	HOLD UP TIME (Typ.)	30ms/230VAC		20ms/115VAC at full load																							
	VOLTAGE RANGE Note.6	90 ~ 264VAC		127 ~ 370VDC																							
	FREQUENCY RANGE	47 ~ 63Hz																									
FUNCTION	POWER FACTOR (Typ.)	PF>0.93/230VAC		PF>0.98/115VAC at full load																							
	EFFICIENCY (Typ.)	84%		84%		83%		83%																			
	AC CURRENT (Typ.)	1.8A/115VAC		0.9A/230VAC																							
	INRUSH CURRENT (Typ.)	COLD START 35A/115VAC		70A/230VAC																							
	LEAKAGE CURRENT (max.) Note.7	Earth leakage current < 160 μ A/264VAC , Touch current < 100 μ A/264VAC																									
	OVERLOAD	105 ~ 135% rated output power Protection type : Hiccup mode, recovers automatically after fault condition is removed																									
PROTECTION	OVER VOLTAGE	Ch1: 5.7 ~ 6.8V Protection type : Shut down o/p voltage, re-power on to recover																									
	OVER TEMPERATURE	TSW1: Shut down o/p voltage, recovers automatically after temperature goes down TSW2: Shut down o/p voltage, re-power on to recover																									
	5V STANDBY (G model)	5Vsb : 5V@0.6A without fan, 0.8A with fan 20.5CFM ; Tolerance ± 2%, ripple : 50mVp-p(max.)																									
ENVIRONMENT	PS-ON INPUT SIGNAL (G model)	Power on: PS-ON = "Hi" or "> 2 ~ 5V" ; Power off: PS-ON = "Low" or "< 0 ~ 0.5V"																									
	POWER GOOD / POWER FAIL	500ms>PG>10ms PF>1ms																									
SAFETY & EMC (Note 10)	WORKING TEMP.	-20 ~ +70°C (Refer to "Derating Curve")																									
	WORKING HUMIDITY	20 ~ 90% RH non-condensing																									
	STORAGE TEMP., HUMIDITY	-40 ~ +85°C, 10 ~ 95% RH non-condensing																									
	TEMP. COEFFICIENT	±0.03%/°C (0 ~ 50°C)																									
	VIBRATION	10 ~ 500Hz, 2G 10min./1cycle, 60min. each along X, Y, Z axes																									
	OPERATING ALTITUDE Note.8	3000 meters																									
OTHERS	SAFETY STANDARDS	IEC 60601-1:2005+A1, TUV BS EN/ EN 60601-1:2006+A1+A12+A2, ANSI/AAMI ES60601-1:2005+A2 CAN/CSA C22.2 No. 60601-1:2014+A2, EAC TP TC 004 approved; Design refer to BS EN/EN60335-1(by request)																									
	ISOLATION LEVEL	Primary-Secondary: 2xMOPP, Primary-Earth:1xMOPP, Secondary-Earth:1xMOPP																									
	WITHSTAND VOLTAGE	I/P-O/P:4KVAC I/P-FG:2KVAC O/P-FG:1.5KVAC																									
	ISOLATION RESISTANCE	I/P-O/P, I/P-FG, O/P-FG:100M Ohms / 500VDC / 25°C / 70% RH																									
	EMC EMISSION	Parameter	Standard			Test Level / Note																					
	Conducted emission	BS EN/EN55011 (CISPR11)			Class B																						
	Radiated emission	BS EN/EN55011 (CISPR11)			Class B																						
	Harmonic current	BS EN/EN61000-3-2			Class A																						
	Voltage flicker	BS EN/EN61000-3-3			-----																						
	EMC IMMUNITY	Parameter	Standard			Test Level / Note																					
NOTE	ESD	BS EN/EN61000-4-2			Level 4, 15KV air ; Level 4, 8KV contact																						
	RF field susceptibility	BS EN/EN61000-4-3			Level 3, 10V/m(80MHz~2.7GHz) Table 9, 9~28V/m(385MHz~5.78GHz)																						
	EFT bursts	BS EN/EN61000-4-4			Level 3, 2KV																						
	Surge susceptibility	BS EN/EN61000-4-5			Level 3, 2KV/Line-FG ; 1KV/Line-Line																						
	Conducted susceptibility	BS EN/EN61000-4-6			Level 3, 10V																						
	Magnetic field immunity	BS EN/EN61000-4-8			Level 4, 30A/m																						
	Voltage dip, interruption	BS EN/EN61000-4-11			100% dip 1 periods, 30% dip 25 periods, 100% interruptions 250 periods																						
OTHERS	MTBF	1719.1K hrs min. Telcordia SR-332 (Bellcore) ; 175.1K hrs min. MIL-HDBK-217F (25°C)																									
	DIMENSION (L*W*H)	PCB type: 127*76.2*34.6mm or 5" * 3" * 1.36" inch																									
NOTE	PACKING	0.33Kg; 36pcs/12.9Kg/0.96CUFT																									
	1. All parameters NOT specially mentioned are measured at 230VAC input, rated load and 25°C of ambient temperature. 2. The rated power includes 5Vsb @ 0.8A. 3. The rated power includes 5Vsb @ 0.6A. 4. Ripple & noise are measured at 20MHz of bandwidth by using a 12" twisted pair-wire terminated with a 0.1 μ F & 47 μ F parallel capacitor. 5. Tolerance : includes set up tolerance, line regulation and load regulation. 6. Derating may be needed under low input voltages. Please check the derating curve for more details. 7. Touch current was measured from primary input to DC output. 8. The ambient temperature derating of 3.5°C/1000m with fanless models and of 5°C/1000m with fan models for operating altitude higher than 2000m(6500ft). 9. HS1,HS2 & HS3 can not be shorted. 10. The power supply is considered a component which will be installed into a final equipment. All the EMC tests are been executed by mounting the unit on a 360mm*360mm metal plate with 1mm of thickness. The final equipment must be re-confirmed that it still meets EMC directives. For guidance on how to perform these EMC tests, please refer to "EMI testing of component power supplies." (as available on https://www.meanwell.com/Upload/PDF/EMI_statement_en.pdf)	※ Product Liability Disclaimer : For detailed information, please refer to https://www.meanwell.com/serviceDisclaimer.aspx																									


SPECIFICATION for Enclosed Type(optional)

MODEL	RPT(G)-160A-C			RPT(G)-160B-C			RPT(G)-160C-C			RPT(G)-160D-C				
OUTPUT	OUTPUT NUMBER	CH1	CH2	CH3	CH1	CH2	CH3	CH1	CH2	CH3	CH1	CH2	CH3	
	DC VOLTAGE	5V	12V	-5V	5V	12V	-12V	5V	15V	-15V	5V	12V	24V	
	RATED (20.5CFM)	13.3A	5.2A	0.95A	13.3A	4.8A	0.95A	13.3A	3.4A	0.95A	10.5A	4.8A	1.14A	
	CURRENT RANGE (20.5CFM)	0.6 ~ 13.3A	0.2 ~ 5.2A	0.1 ~ 0.95A	0.6 ~ 13.3A	0.2 ~ 4.8A	0.1 ~ 0.95A	0.6 ~ 13.3A	0.1 ~ 3.4A	0.1 ~ 0.95A	0.3 ~ 10.5A	0.2 ~ 4.8A	0.15 ~ 1.14A	
	RANGE (convection)	0.6 ~ 8.5A	0.2 ~ 3.6A	0.1 ~ 0.57A	0.6 ~ 8.5A	0.2 ~ 3.2A	0.1 ~ 0.76A	0.6 ~ 8.5A	0.1 ~ 2.5A	0.1 ~ 0.76A	0.3 ~ 7.6A	0.2 ~ 2.5A	0.15 ~ 0.95A	
	RATED POWER	20.5CFM Note.2	137.7W			139.5W			135.8W			141.5W		
	Convection Note.3	91.6W			93W			94.4W			93.8W			
	RIPPLE & NOISE (max.) Note.4	60mVp-p	80mVp-p	120mVp-p	60mVp-p	100mVp-p	100mVp-p	60mVp-p	80mVp-p	100mVp-p	80mVp-p	100mVp-p	120mVp-p	
	VOLTAGE ADJ. RANGE	CH1:5 ~ 5.5V												
	VOLTAGE TOLERANCE Note.5	±2.0%	±5.0%	-5,+7%	±2.0%	±5.0%	-4,+5%	±2.0%	±4.0%	±8.0%	±2.0%	±5.0%	+7,-5%	
INPUT	LINE REGULATION	±0.5%	±1.0%	±1.0%	±0.5%	±1.0%	±1.0%	±0.5%	±1.0%	±1.0%	±0.5%	±1.0%	±1.0%	
	LOAD REGULATION	±1.5%	±3.0%	-5,+6%	±1.5%	±3.0%	-4,+5%	±2.0%	±3.0%	±8.0%	±1.5%	±3.0%	-3,+4%	
	SETUP, RISE TIME	1800ms, 30ms/230VAC			3500ms, 30ms/115VAC at full load									
	HOLD UP TIME (Typ.)	30ms/230VAC			20ms/115VAC at full load									
	VOLTAGE RANGE Note.6	90 ~ 264VAC			127 ~ 370VDC									
	FREQUENCY RANGE	47 ~ 63Hz												
FUNCTION	POWER FACTOR (Typ.)	PF>0.93/230VAC			PF>0.98/115VAC at full load									
	EFFICIENCY (Typ.)	84%			84%			83%			83%			
	AC CURRENT (Typ.)	1.8A/115VAC			0.9A/230VAC									
	INRUSH CURRENT (Typ.)	COLD START 35A/115VAC			70A/230VAC									
	LEAKAGE CURRENT (max.) Note.7	Earth leakage current < 160 μ A/264VAC , Touch current < 100 μ A/264VAC												
	OVERLOAD	105 ~ 135% rated output power			Protection type : Hiccup mode, recovers automatically after fault condition is removed									
PROTECTION	OVER VOLTAGE	Ch1: 5.7 ~ 6.8V			Protection type : Shut down o/p voltage, re-power on to recover									
	OVER TEMPERATURE	TSW1: Shut down o/p voltage, recovers automatically after temperature goes down			TSW2: Shut down o/p voltage, re-power on to recover									
ENVIRONMENT	5V STANDBY (G model)	5Vsb : 5V@0.6A without fan, 0.8A with fan 20.5CFM ; Tolerance ± 2%, ripple : 50mVp-p(max.)												
	PS-ON INPUT SIGNAL (G model)	Power on: PS-ON = "Hi" or > 2 ~ 5V" ; Power off: PS-ON = "Low" or < 0 ~ 0.5V"												
	POWER GOOD / POWER FAIL	500ms>PG>10ms			PF>1ms									
SAFETY & EMC (Note 10)	WORKING TEMP.	-20 ~ +70°C (Refer to "Derating Curve")												
	WORKING HUMIDITY	20 ~ 90% RH non-condensing												
	STORAGE TEMP., HUMIDITY	-40 ~ +85°C, 10 ~ 95% RH non-condensing												
	TEMP. COEFFICIENT	±0.03%/°C (0 ~ 50°C)												
	VIBRATION	10 ~ 500Hz, 2G 10min./1cycle, 60min. each along X, Y, Z axes												
	OPERATING ALTITUDE Note.8	3000 meters												
	SAFETY STANDARDS	Design refer to IEC60601-1, EAC TP TC 004, TUV BS EN/EN60601-1(Pending for CB/TUV)												
	ISOLATION LEVEL	Primary-Secondary: 2xMOPP, Primary-Earth:1xMOPP, Secondary-Earth:1xMOPP												
	WITHSTAND VOLTAGE	I/P-O/P:4KVAC I/P-FG:2KVAC O/P-FG:1.5KVAC												
	ISOLATION RESISTANCE	I/P-O/P, I/P-FG, O/P-FG:100M Ohms / 500VDC / 25°C / 70% RH												
OTHERS	EMC EMISSION	Parameter	Standard			Test Level / Note								
		Conducted emission	BS EN/EN55011 (CISPR11)			Class B								
		Radiated emission	BS EN/EN55011 (CISPR11)			Class B								
		Harmonic current	BS EN/EN61000-3-2			Class A								
	EMC IMMUNITY	Voltage flicker	BS EN/EN61000-3-3			-----								
		BS EN/EN55035, BS EN/EN60601-1-2												
		Parameter	Standard			Test Level / Note								
		ESD	BS EN/EN61000-4-2			Level 4, 15KV air ; Level 4, 8KV contact								
		RF field susceptibility	BS EN/EN61000-4-3			Level 3, 10V/m (80MHz~2.7GHz) Table 9, 9~28V/m (385MHz~5.78GHz)								
		EFT bursts	BS EN/EN61000-4-4			Level 3, 2KV								
NOTE	Surge susceptibility	BS EN/EN61000-4-5			Level 3, 2KV/Line-FG ; 1KV/Line-Line									
	Conducted susceptibility	BS EN/EN61000-4-6			Level 3, 10V									
	Magnetic field immunity	BS EN/EN61000-4-8			Level 4, 30A/m									
	Voltage dip, interruption	BS EN/EN61000-4-11			100% dip 1 periods, 30% dip 25 periods, 100% interruptions 250 periods									
	MTBF	1719.1K hrs min. Telcordia SR-332 (Bellcore) ; 175.1K hrs min. MIL-HDBK-217F (25°C)												
	DIMENSION	Enclosed type: 130*86*43mm or 5.11" * 3.39" * 1.69" inch												
	PACKING	0.49Kg; 24pcs/12.8Kg/0.77CUFT												
	1. All parameters NOT specially mentioned are measured at 230VAC input, rated load and 25°C of ambient temperature.													
	2. The rated power includes 5Vsb @ 0.8A.													
	3. The rated power includes 5Vsb @ 0.6A.													
	4. Ripple & noise are measured at 20MHz of bandwidth by using a 12" twisted pair-wire terminated with a 0.1 μ F & 47 μ F parallel capacitor.													
	5. Tolerance : includes set up tolerance, line regulation and load regulation.													
	6. Derating may be needed under low input voltages. Please check the derating curve for more details.													
	7. Touch current was measured from primary input to DC output.													
	8. The ambient temperature derating of 3.5°C/1000m with fanless models and of 5°C/1000m with fan models for operating altitude higher than 2000m(6500ft).													
	9. HS1,HS2 & HS3 can not be shorted.													
	10. The power supply is considered													


■ Block Diagram



■ Derating Curve




■ Output Derating VS Input Voltage



■ Mechanical Specification


Unit:mm

- PCB Type: RPT-160(G)





● Enclosed Type: RPT-160(G)-C


Case No.247A Unit:mm




Side View




Side View




5cm
Air flow direction
Top View
FAN 20.5CFM
65



Side View




Side View



Bottom View

※ Mounting Instruction

Hole No.	Recommended Screw Size	MAX. Penetration Depth L	Recommended mounting torque
① ②	M3	2mm	4~6Kgf-cm



AC Input Connector (CN1) : JST B3P-VH or equivalent

Pin No.	Assignment	Mating Housing	Terminal
1	AC/L		
2	No Pin	JST VHR or equivalent	JST SVH-21T-P1.1 or equivalent
3	AC/N		

DC Output Connector (CN2) : JST B8P-VH or equivalent

Pin No.	Assignment	Mating Housing	Terminal
1,2,3,4	COM		
5,6	CH1	JST VHR or equivalent	JST SVH-21T-P1.1 or equivalent
7	CH2		
8	CH3		

Power Good Connector(CN3):JST B2B-XH or equivalent

Pin No.	Status	Mating Housing	Terminal
1	PG	JST XHP or equivalent	JST SXH-001T-P0.6 or equivalent
2	GND		

5VSB Connector(CN901) : JST B-XH or equivalent

Pin No.	Assignment	Mating Housing	Terminal
1	PS/ON		
2,4	GND	JST XHP or equivalent	JST SXH-001T or equivalent
3	5VSB		

⚠ 1.HS1,HS2,HS3 can not be shorted
2.M1 and M2 are Safety ground and should all be grounded.

※ Note: 1. The PCB type (Blank Type) model delivers EMI Class B for both conducted emission and radiated emission for the power supply, when configured into either Class I (with FG).
 2. The enclosed type (-C type) model is not suitable for configuration within a Class II (no FG) system, but suggested within a Class I (with FG) system.
 3. Mounting Instruction for Enclosed type only.

■ INSTALLATION MANUAL

Please refer to : <http://www.meanwell.com/manual.html>