

1-1734368-2 Product Details

 Share  Print  Email



1-1734368-2

TE Internal Number: 1-1734368-2

 Active

 View 3D PDF

Connector System For IEEE1394 Serial Bus

 Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Size = Standard
- IEEE 1394 Series
- Receptacle
- 1 Ports
- Applies To Printed Circuit Board

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- [SOCKET ASS'Y, R/A, 6 POS., FLAT SMT, IEEE 1394](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files: ([CAD Format & Compression Information](#))

- [2D Drawing](#) (DXF, Version 0)
- [3D Model](#) (IGES, Version 0)
- [3D Model](#) (STEP, Version 0)

[List all Documents](#)

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Size = Standard
- Series = IEEE 1394
- Gender = Receptacle
- Number of Ports = 1
- Orientation = Right Angle
- PCB Thickness (Minimum) (mm [in]) = 1.60 [0.063]

Mechanical Attachment:

- Mount Location = Top

Termination Features:

- Termination Method = Solder

Body Features:

- Panel Ground = Without
- PCB Mount Retention Type = Straight Leg
- Front Shell Plating = Nickel over Copper
- Backshell Plating = Nickel over Copper
- Assembly Process Feature = None
- Locating Post(s) = With
- Number of Positions = 6

Contact Features:

- Contact Termination Type = Surface Mount
- Contact Plating, Mating Area, Material = Gold
- Contact Plating, Mating Area, Thickness (µm [µin]) = 0.762 [30]

Housing Features:

- Housing Color = Natural

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- Applies To = Printed Circuit Board

Packaging Features:

- [Packaging Method](#) = Tape & Reel

Other:

- Brand = AMP

Corporate Information

[Who We Are](#)

[Investors](#)

[News Room](#)

[Supplier Portal](#)

[Careers](#)

Quick Links

[Check Distributor Inventory](#)

[Cross Reference](#)

[Find Documents & Drawings](#)

[Product Compliance Support Center](#)

[Site Map](#)

Customer Support

[Email or Chat With Us](#)

[Find a Phone Number](#)

[Search Knowledge Base](#)

[Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

