




"A"  LOCKED IN THREE POSITIONS	"B"  LOCKED IN CENTER AND EXTREME POSITION (KEYWAY SIDE)	"D"  LOCKED OUT OF CENTER POSITION	"E"  LOCKED IN CENTER POSITION	"F"  LOCKED IN EXTREME POSITION (OPPOSITE KEYWAY)	"G"  LOCKED IN EXTREME POSITION (KEYWAY SIDE)
"H"  LOCKED OUT OF CENTER AND EXTREME POSITION (KEYWAY SIDE)	"J"  LOCKED OUT OF CENTER AND EXTREME POSITION (OPPOSITE KEYWAY)	"K"  LOCKED IN CENTER AND EXTREME POSITION (OPPOSITE KEYWAY)	"L"  LOCKED OUT OF EXTREME POSITION (KEYWAY SIDE)	"M"  LOCKED OUT OF AND INTO EXTREME POSITION (OPPOSITE KEYWAY)	"N"  LOCKED OUT OF EXTREME POSITION (OPPOSITE KEYWAY)
"P"  LOCKED OUT OF AND INTO EXTREME POSITION (KEYWAY SIDE)					



- ### NOTES:
- ① - UNIT INCLUDES "23SX39-T2 SMOOTH GOLD CONTACT" (4)
 - 2 - SWITCHES DO NOT NECESSARILY OPERATE SIMULTANEOUSLY
 - 3 - TERMINALS ARE PLATED FOR SOLDERING
 - ④ SWITCH NUMBERS MARKED ON END OF BASIC SWITCHES
 - ⑤ TERMINAL DESIGNATION STAMPED ON BOTH SIDES OF UNIT
 - ⑥ DULL FINISH ON LEVER AND BUSHING
 - ⑦ FLAT WHITE RESILIENT SILICONE (50 DUROMETER APPROX)
 - ⑧ SUFFIX LETTER MUST BE ADDED FOR DESIRED TYPE TOGGLE LOCKING (SEE CHART FOR RECOMMENDED LOCKING COMBINATIONS)
 - 9 - FOR REPLACEMENT BUTTON SEE MICRO SWITCH CAT. LISTING 15PA90-6W
 - ⑩ HARDWARE FURNISHED ASSEMBLED WITH SWITCH OR IN PACKET 15PA313-AT PER MIL-PRF-8805
 - 11 - REPLACEMENT MOUNTING HARDWARE PACKET 15PA313-AT

CHARACTERISTICS		ELECTRICAL DATA			DESIGN UNITS: INCH			DRAWN	DVM	30APR08	Honeywell					
PULL OUT FORCE ----- 3 lb MIN - 5 lb MAX		CONTACT ARRANGEMENT SPDT (4) 			TOLERANCES UNLESS NOTED:			CHECK	TSG	30APR08						
								NO PLACES X ± 0.03			THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.			TITLE TOGGLE SWITCH		
					ONE PLACE .X ± 0.015											
					TWO PLACE .XX ± 0.005			INTERPRET PER ASME Y14.5M-1994 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY			SIZE	TYPE	CAGE CODE	DRAWING NAME		REV
					THREE PLACE .XXX ±						C	I	-	64AT811-1E		A
					ANGLES X ±			RASTER			SCALE	2 : 1		SHEET	OF	
					THIRD ANGLE PROJECTION 											