

NLV32T-033J-EF

Product Status	Production
Applications	Commercial Grade
	No Directivity
Feature	Wire Wound
	Ferrite Core
Series   Type	NLV32-EF
Brand	TDK
Environmental Compliance	 RoHS  REACH  Halogen Free  Lead Free



Size	
Length(L)	3.20mm $\pm 0.20$ mm
Width(W)	2.50mm $\pm 0.20$ mm
Thickness   Height	2.20mm $\pm 0.20$ mm
Recommended Land Pattern (A)	1.20mm Nom.
Recommended Land Pattern (B)	2.00mm Nom.
Recommended Land Pattern (C)	2.00mm Nom.

Electrical Characteristics	
Inductance	33nH $\pm 5\%$ at 100MHz
Rated Current	450mA
DC Resistance [Typ.]	
DC Resistance [Max.]	240m $\Omega$
Self Resonant Frequency [Min.]	1.4GHz
Self Resonant Frequency [Typ.]	
Q [Min.]	25 at 100MHz
Q [Typ.]	

Other	
Operating Temp. Range	-40 to 105°C (Including Self-Temp. Rise)
Soldering Method	Wave (Flow) Reflow Iron Soldering
AEC-Q200	NO
Packing	Embossed (Plastic)Taping [180mm Reel]
Package Quantity	2000pcs
Weight	0.05g





! Images are for reference only and show exemplary products.

! This PDF document was created based on the data listed on the TDK Corporation website.

! All specifications are subject to change without notice.


NLV32T-033J-EF

## Characteristic Graphs (This is reference data, and does not guarantee the products characteristics.)



! Images are for reference only and show exemplary products.  
! This PDF document was created based on the data listed on the TDK Corporation website.  
! All specifications are subject to change without notice.

## Associated Images



! Images are for reference only and show exemplary products.  
! This PDF document was created based on the data listed on the TDK Corporation website.  
! All specifications are subject to change without notice.