

### OPERATING CONDITIONS / ELECTRICAL CHARACTERISTICS

| Parameters                  | Conditions                       | ECS-L2 (+2.5V) |      |        | ECS-L3 (+3.3V) |      |        | Units |
|-----------------------------|----------------------------------|----------------|------|--------|----------------|------|--------|-------|
|                             |                                  | MIN            | TYP  | MAX    | MIN            | TYP  | MAX    |       |
| Frequency Range             |                                  | 10.000         |      | 1500.0 | 10.000         |      | 1500.0 | MHz   |
| Operating Temperature       | Standard                         | 0              |      | +70    | 0              |      | +70    | °C    |
|                             | Extended (N Option)              | -40            |      | +85    | -40            |      | +85    | °C    |
| Storage Temperature         |                                  | -55            |      | +125   | -55            |      | +125   | °C    |
| Supply Voltage              | V <sub>DD</sub>                  | +2.375         | +2.5 | +2.625 | +3.135         | +3.3 | +3.465 | VDC   |
| Frequency Stability *       | Option A                         |                |      | ±100   |                |      | ±100   | ppm   |
|                             | Option B                         |                |      | ±50    |                |      | ±50    | ppm   |
|                             | Option C                         |                |      | ±25    |                |      | ±25    | ppm   |
|                             | Option D                         |                |      | ±20    |                |      | ±20    | ppm   |
| Input Current               | 10.0 ~ 100.0 MHz                 |                |      | 16     |                |      | 18     | mA    |
|                             | 100.1 ~ 250.0 MHz                |                |      | 18     |                |      | 20     | mA    |
|                             | 250.1 ~ 500 MHz                  |                |      | 21     |                |      | 22     | mA    |
|                             | 500.1 ~ 1500.0 MHz               |                |      | 26     |                |      | 28     | mA    |
| Output Symmetry             | @ 50% V <sub>DD</sub> level      |                |      | 45/55  |                |      | 45/55  | %     |
| Output Load                 | Load between each Output         |                |      | 100    |                |      | 100    | Ω     |
| Output Enable               | Pin 1 **                         | 0.7%           |      |        | 0.7%           |      |        | Vdd   |
| Output Disable              | Pin 1                            |                |      | 0.3%   |                |      | 0.3%   | Vdd   |
| Disable Current             |                                  |                | 16   |        | 16             |      |        | mA    |
| Output Enable Time          |                                  |                |      | 200    |                |      | 200    | ns    |
| Output Disable Time         | Pin 1 = VIL                      |                |      | 50     |                |      | 50     | ns    |
| Differential Output Voltage |                                  | 175            | 350  |        | 175            | 350  |        | mV    |
| Offset Voltage              |                                  |                | 1.25 |        |                | 1.25 |        | V     |
| Rise and Fall Times         | 10% V <sub>DD</sub> to 90% Level | 150            | 350  | 500    | 150            | 350  | 500    | pS    |
| Aging                       | @ +25°C (first year)             |                |      | ±2     |                |      | ±2     | PPM   |
| Start-up Time               | @ +25°C (first year)             |                |      | 10     |                |      | 10     | ms    |
| Absolute Voltage Range      |                                  |                |      | +3.63  |                |      | +3.63  | VDC   |
| Moisture Sensitivity Level  |                                  | 1              |      |        |                |      |        |       |
| Termination Finish          |                                  | Au             |      |        |                |      |        |       |
| ESD Sensitivity             | Human Body Model                 | 3kV Max.       |      |        |                |      |        |       |

\*Note: Inclusive of 25 °C tolerance, operating temperature, input voltage change, load change, shock and vibration.

\*\*Note: Internal pull-up resistor active output if pin 1 is left open.


#### Part Numbering Guide: Example ECX-L35BN-156.250

| Series                 | Voltage                | Package Size (mm)                                         | Stability                                                     | Operating Temperature                                                     | Frequency          |
|------------------------|------------------------|-----------------------------------------------------------|---------------------------------------------------------------|---------------------------------------------------------------------------|--------------------|
| ECX-L<br>(LVDS Output) | 2 = +2.5V<br>3 = +3.3V | 2 = 2.5 x 2<br>3 = 3.2 x 2.5<br>5 = 5 x 3.25<br>7 = 7 x 5 | A = ± 100 ppm<br>B = ± 50 ppm<br>C = ± 25 ppm<br>D = ± 20 ppm | L = -10 ~ +70°C<br>M = -20 ~ +70°C<br>N = -40 ~ +85°C<br>P = -40 ~ +105°C | Customer Specified |

### Phase Noise and Jitter Data (typical)

| SSB Phase Noise Data (dBc/Hz typical)      | Frequency (offset) | 77.760 | 122.880 | 125.000 | 156.250 | 212.5 | 491.520 | 622.080 | 1000 | 1250 |
|--------------------------------------------|--------------------|--------|---------|---------|---------|-------|---------|---------|------|------|
| 10 Hz                                      |                    | -64    | -68     | -63     | -55     | -62   | -61     | -48     | -52  | -42  |
| 100 Hz                                     |                    | -84    | -99     | -94     | -85     | -93   | -86     | -85     | -82  | -81  |
| 1 KHz                                      |                    | -118   | -113    | -113    | -109    | -105  | -100    | -101    | -93  | -93  |
| 10 KHz                                     |                    | -128   | -119    | -118    | -116    | -113  | -105    | -102    | -97  | -96  |
| 100 KHz                                    |                    | -137   | -120    | -119    | -118    | -115  | -105    | -103    | -97  | -97  |
| 1 MHz                                      |                    | -145   | -140    | -137    | -139    | -135  | -126    | -124    | -116 | -119 |
| 5 MHz                                      |                    | -152   | -142    | -146    | -146    | -143  | -137    | -133    | -127 | -129 |
| Phase Jitter pS<br>12 KHz ~ 20 MHz,<br>RMS |                    | 0.9    | 0.8     | 1.1     | 0.9     | 1.0   | 1.1     | 1.2     | 1.5  | 1.1  |


### Phase Noise Plot of ECX-L35BN-77.760 (typical)



| Package Data |                              |
|--------------|------------------------------|
| Item         | Description                  |
| Lid          | Metal                        |
| Base         | Ceramic                      |
| Plating      | Gold/Nickel<br>Surface/Under |


**Dimensions (mm)**

**7 = 7x5 Package**




*Figure 1) Top, Side, Bottom & Land*

**5 = 5x3.2 Package**




*Figure 2) Top, Side, Bottom & Land*

**3 = 3.2x2.5 Package**




*Figure 3) Top, Side, Bottom & Land*

**2 = 2.5x2 Package**



*Figure 4) Top, Side, Bottom & Land*

**Suggested Reflow Profile**



**Pin Connections**

| Pin # | Function             |
|-------|----------------------|
| 1     | O/E or No Connect    |
| 2     | No Connect           |
| 3     | Ground               |
| 4     | Differential Output  |
| 5     | Complementary Output |
| 6     | Supply Voltage       |