



Technical Data

31.10.2022

Heat shrinkable tubing 2:1 - flexible and coloured
HFT-A - self extinguishing

HFT-A-19.0/9.5

Article Number 305-19000



Material: Polyolefin, cross-linked (PO-X)
Colour: Black (BK)

Supplied Ø D min.: 19.0 mm

Recov. Ø d max.: 9.5 mm

Wall (WT): 0.80 mm

Shrink Ratio: 2:1

Longitudinal Change After Shrinkage: -5% max.

Min. Shrink Temperature - °C: +135 °C

Test Method

Flammability: self-extinguishing, UL 224 VW-1

Operating Temperature - °C: -55 °C to +135 °C

Heat Shock Test: 4h/200°C

Tensile Strength at Heat Shock: 13 MPa

Elongation at Heat Shock: 390 %

Behaviour At Low Temperature: not cracking

IEC 60684-2

Dielectric Strength: >21 kV/mm

IEC 60684-2

Insulation Class: B (VDE 0530)

Tensile Strength: 14 MPa

IEC 60684-2

Elongation at break: 400%

IEC 60684-2

Specifications: CLASS 903201, UL 224, VG 95343-5:2016-10



We assume no responsibility that the Product will be used for the intended purpose, this is beyond our control. It's up to the customer to check the suitability for a specific application by means of tests. Technical changes and errors reserved