
Part Number : 2093250003
Product Description : KK Plus 300 Terminal Position Assurance (TPA) Retainer, 3 Circuits, Natural
Series Number : 209325
Status : Active
Product Category : Connector Accessories



Documents and Resources

Drawings

2093250003_sd.pdf

2093250000-PK-000.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

2092080000-PS-000.pdf

2092080000-TS-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains 1,1'-(Ethane-1,2-diyl)bis[pentabromobenzene] per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Downloaded from Arrow.com.

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Accessories
Series	209325
Description	KK Plus 300 Terminal Position Assurance (TPA) Retainer, 3 Circuits, Natural
Component Type	Terminal Position Assurance (TPA)
Product Name	KK Plus
UPC	193264185825

Agency

UL	E29179

Physical

Circuits (Loaded)	3
Circuits (maximum)	3
Color - Resin	Natural
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	0.072/g
Number of Rows	1
Packaging Type	Bag
Temperature Range - Operating	-40° to +105°C

Downloaded from Arrow.com.

Mates With / Use With

Use with Part(s)

Description	Part Number
KK Plus 300 Receptacle Housing, 3.00mm Pitch, Single Row, 3 Circuits, UL 94V-0, Black, Glow-Wire Capable	2092090003

Downloaded from Arrow.com.