


CUSTOMER PRINT

PART NUMBER: W4282-1XPG-3ES


- NOTES:
1. ALL PARTS TO BE BULK PACKED.
 2. CONTACTS ASSEMBLED INTO CONNECTOR. SOLDER CUPS FACING TOP KEY.
 3. BACK WELL FILLED WITH EPOXY.
 4. ALL DIMENSIONS ARE REFERENCE ONLY EXCEPT WHERE NOTED WITH A TOLERANCE. DIMENSIONS IN BRACKETS [] ARE METRIC.

ASS'Y P/N	CONTACTS	HOLE POS. CLOSED
W4282-10PG-3ES	10 - #20	11, 12
W4282-11PG-3ES	11 - #20	12
W4282-12PG-3ES	12 - #20	NONE
W4282-1XPG-3ES		


NO. OF CONTACTS





FACE VIEW
W4282-10PG-3ES
10-POS.




FACE VIEW
W4282-11PG-3ES
11-POS.




FACE VIEW
W4282-12PG-3ES
12-POS.




13/16-27 UNS-2A
MOD. THREAD



EPOXY FILLED
SEE NOTE 3




WIRE VIEW
W4282-10PG-3ES - 10-POS. (11&12 CLOSED)
W4282-11PG-3ES - 11-POS. (12 CLOSED)
W4282-12PG-3ES - 12-POS. (ALL OPEN)



RECOMMENDED
PANEL CUTOUT
STANDARD MULTI-CON-X

CUSTOMER APPROVAL	
THIS DOCUMENT CONTAINS CONFIDENTIAL INFORMATION PROPRIETARY TO CONXALL CORPORATION. ANY REPRODUCTION, DISCLOSURE, OR USE OF THIS DOCUMENT /INFORMATION IS EXPRESSLY PROHIBITED UNLESS AUTHORIZED IN WRITING BY CONXALL CORPORATION.	
APPROVED BY:	_____
DATE:	_____

A	PAK	09/12/19	DRAWING CREATED AND RELEASED PER DOR 10-2523JS-1		
REV.	INIT.	DATE	DESCRIPTION		
	PAK	10/03/14	ORIG. DRAWN BY:	DATE:	 601 E. WILDWOOD VILLA PARK, IL 60181
ALL INFORMATION ILLUSTRATED IS THE PROPERTY OF "CONXALL CORPORATION". UNAUTHORIZED DUPLICATION OR DISTRIBUTION OF THIS DOCUMENT IS PROHIBITED.			CHECKED BY:		
ALL UNITS ARE IN FEET, INCHES, FRACTION OF INCHES AND DECIMALS.			APPROVED BY:		TITLE: PANEL PIN, W/ EPOXY #20 SOLDER, 12-POS. MULTI-CON-X, E-KEY, WEATHER RESISTANT STANDARD PRODUCT
UNLESS OTHERWISE SPECIFIED TOLERANCES: 3 PLACE DECIMALS ±.005 ANGLES ±1° FRACTIONS ±1/16			SCALE: NTS	SIZE: B	
△ = CRITICAL CHARACTERISTIC FLAG PER SPEC. XXXX			SHEET: 1 OF 1	DIRECTORY: SLW	PART NUMBER: W4282-1XPG-3ES
					REV A