

**Q 2 SAK2.5****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image** Similar to illustration

Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

**General ordering data**

Version	Cross-connector (terminal), when screwed in, grey, 24 A, Number of poles: 2, Pitch in mm (P): 6.00, Insulated: No, Width: 11.5 mm
Order No.	<a href="#">0337000000</a>
Type	Q 2 SAK2.5
GTIN (EAN)	4008190005801
Qty.	50 ST

## Q 2 SAK2.5

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

ROHS	Conform
------	---------

## Dimensions and weights

Depth	20.5 mm	Depth (inches)	0.8071 inch
Height	6 mm	Height (inches)	0.2362 inch
Width	11.5 mm	Width (inches)	0.4528 inch
Net weight	3.44 g		

## Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C
---------------------	----------------	---------------------	---------------

## Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

## Material data

Material	CuSn	Colour	grey
----------	------	--------	------

## System specifications

Version	for cross-connection link
---------	---------------------------

## Additional technical data

Type of fixing	when screwed in	Installation advice	Direct mounting
Explosion-tested version	No		

## Cross-connector

Number of cross-connected terminals	2	Type	Cross-connector
Rated current, 2-pole	41 A	Rated current, multi-pole	41 A

## Dimensions

Pitch in mm (P)	6.00 mm
-----------------	---------

## General

Number of poles	2	Installation advice	Direct mounting
-----------------	---	---------------------	-----------------

## Rating data

Rated current	24 A
---------------	------

## Classifications

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ETIM 9.0	EC000489
ETIM 10.0	EC000489	ECLASS 9.0	27-14-11-40
ECLASS 9.1	27-14-11-40	ECLASS 10.0	27-14-11-40

## Technical data

ECLASS 11.0	27-14-11-40	ECLASS 12.0	27-14-11-40
ECLASS 13.0	27-25-03-03	ECLASS 14.0	27-25-03-03
ECLASS 15.0	27-25-03-03		