




used for: D-SUB

61.1^{+0.14}_{-0.11}

22.1±0.1

19.33±0.1

16.56±0.1

13.82±0.1

11.05±0.1

8.28±0.1

5.54±0.1

2.77±0.1

∅3.1±0.1 (2x)

∅1.0^{+0.1}₋₀ (50x)

P.C.B. EDGE

FRONTPANEL

2.84±0.1

2.84±0.1

5±0.1

1.4±0.1

4.14±0.1

6.91±0.1

9.68±0.1

12.42±0.1


15.19±0.1

17.96±0.1

20.7±0.1

APPROVAL * FREIGABE * DEBLOCAGE * AUTORIZACION * APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL * FREIGABE * DEBLOCAGE * AUTORIZACION * APPROVAL	

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH DO NOT ALTER CAD DRAWING BY HAND

				tolerance		 dim. in mm
rev.	description	date	name			
		2005		date		name
		drawn	12.04.			Schmidt
		appd.	12.04.			Kühle
		norm	DIN 41652			
		d-old				
						

scale:	2:1
material:	SEE SHEET 1
title:	P.C.B. HOLE DRILLINGS D-SUB FEMALE 90°,50pos.,SOLDER PIN ANGLED with threaded insert, metal bracket and clip
dwg no:	AutoCAD 2004
part no:	SEE SHEET 1
DIN-A	4
sh:2/2	